


9089T-9 8" 脸盆龙头





**订购时请说明颜色编号
**Color code must be specified when ordering

9089T-9 8" 脸盆龙头

安装之前	BEFORE YOU BEGIN
<p>所有的资料是按最新出版的产品资料编写而成。科勒公司保留任何时候不经通知即可改变产品特性、包装或产品可供类型的权利。</p> <p>说明书包括重要的安装、保养及清洁方面的内容，请把这些资料交给用户阅读。</p> <p>注意事项：</p> <ol style="list-style-type: none">一定要先彻底冲洗供水管以清除管道中的杂质。检查供水管有无损坏。如需要，进行替换。遵守当地管路安装条例。尽可能在安装脸盆之前安装水龙头。	<p>All information is based on the latest product information available at the time of publication. Kohler Co. reserves the right to make changes in product characteristics, packaging, or availability at any time without notice.</p> <p>Please leave these instructions for the consumer. They contain important information.</p> <p>NOTES:</p> <ol style="list-style-type: none">Flush the water supply pipes thoroughly to remove debris.Inspect the supply tubing for damage. Replace as necessary.Observe local plumbing codes.If possible, install this faucet before installing the lavatory.
使用说明	HANDLE OPERATION
<p>顺时针旋转左把手为开，逆时针旋转右把手为开。</p>	<p>Left handle opens with turning clockwise, right handle opens with turning counter-clockwise.</p>
安装尺寸	ROUGH-IN DIMENSIONS

<h2>安装步骤</h2>	
<h3>如何安装出水口</h3> <p>从出水口组件(1)上依次拆下螺母(5)、垫片(4)和衬套(3)，垫片(2)保留在出水口组件上，并嵌入出水口底部凹槽内。</p> <p>龙头出水口组件装于脸盆中孔。</p> <p>从脸盆下方依次将衬套(3)、垫片(4)和螺母(5)安装到出水口组件(1)上，调整出水口方向，锁紧螺母(5)以固定出水口。将T型接头(6)旋到出水口底部螺纹上。</p>	<h3>INSTALLATION</h3> <h4>How To Install The Spout</h4> <p>Remove the parts from spout assembly(1) according to the following order: nut(5), washer(4) and sleeve(3). Washer(2) remains on the spout assembly(1), inserting in the groove of the spout assembly.</p> <p>Fit the spout assembly to the center hole of lavatory.</p> <p>Reintall the parts from underside of the lavatory according to the following order: sleeve(3), washer(4) and nut(5). Position the spout. Tighten the nut. Screw the center tee(6) to the spout.</p>
<h3>如何安装阀体</h3> <p>从阀体组件(15)依次拆下把手组件(7)、棘齿圈(9)、装饰盖(10)和垫片(11)。将带有垫圈(12)、垫片(13)和螺母(14)的阀体组件从脸盆的下方插入安装孔。从上方依次装上垫片(11)、装饰盖(10)、棘齿圈(9)。用调节纸板(8)来调整阀体露在脸盆上方的高度，如图所示。根据软管安装需要适当调整阀体出水口朝向。然后用扳手锁紧螺母。</p>	<h3>How To Install The Side Bodies</h3> <p>Remove the parts from side bodies(15) according to the following order: Handle kits(7), ratchet rings(9), escutcheons(10) and washers(11). Insert the side bodies with washers(12), washers(13) and nuts(14) through mounting holes from underside of the lavatory. Reinstall the parts according to the following order: washers(11), escutcheons(10) and ratchet rings(9). Adjust the side bodies' height above the lavatory according to the adjustable cardboard(8). Adjust the outlets of side bodies to connect hoses easily as needed. Tighten the nuts with wrench.</p>
<h3>如何安装把手和软管</h3> <p>将把手组件(7)安装到阀体上(注意：带有红色标记的把手组件装在左侧，且安装之前阀芯处于关闭状态)。</p> <p>将软管(16)两端放上垫片，连接阀体组件(15)的出水口和T型接头(6)。</p> <p>注意：软管(16)只能用于此处。</p>	<h3>How To Install The Handles And The Hoses</h3> <p>Place the handle kits(7) onto the side bodies with the valves closed. (Note: The handle kit with red mark should be installed on the left side) .</p> <p>Connect the outlets of the side bodies(15) and the center tee(6) with the hoses(16) and washers.</p> <p>Note:The hoses(16) should be used here only.</p>

<p>注意：为了安装方便，可以适当旋松T型接头，但不要超过180度。安装必须保证软管水流顺畅。</p> <p>阀处于关闭位置把手的状态如图所示。</p>	 <p>NOTE: For easy installation, loosen the supply tee properly by unscrewing it, but not more than 180 degrees. Ensure that the water inside the hoses flow smoothly.</p> <p>The illustration shown is the correct position of the handles in the off position.</p>
<h3>如何安装排水器</h3> <p>把锁紧螺母(22)、塑料垫片(21)、橡胶垫圈(20)和尾管(19)从排水本体上面取下。在尾管螺纹处须缠绕足以密封的密封胶带或涂合适的密封胶，装回排水本体。把排水本体从脸盆上部孔插入。再依次将橡胶垫圈(小面朝上)、塑料垫片和锁紧螺母从排水本体底部装入。锁紧螺母。</p> <p>在锁紧螺母拧紧后不可调整排水本体的位置，否则会破坏油灰或密封剂密封。</p> <p>注意：如果需要，可直接在排水器盘片(17)底面沿周围涂一圈密封油灰或其它密封剂，而不使用橡胶垫片(18)。</p>	<h3>How To Install The Drain</h3> <p>Remove the locknut(22), plastic washer (21), rubber gasket(20) and tailpiece(19) from the drain body. Supply enough tape or sealant to tailpiece thread. Reinstall the tailpiece. Insert the drain body into the lavatory. Put the rubber gasket (Tapered side up), plastic washer and locknut back to the drain body in turn. Tighten the locknut.</p> <p>Do not reposition the drain after the locknut is tightened, or you may break the putty or sealant seal.</p> <p>NOTE: If needed, apply a ring of plumbers putty or other sealants around the underside of the drain flange(17), instead of using rubber washer(18).</p>
<h3>安装结果检查</h3> <p>确保已拧紧所有的连接处。确保把手在关闭位置。取下起泡器(23)。打开排水器和主供水源，检查泄露。打开冷热水阀，使水流过出水口，除掉杂物，关闭阀。重新装回起泡器。</p>	 <p>INSTALLATION CHECKOUT</p> <p>Ensure that all connections are tight. Ensure that the handles are in the off position. Remove the aerator(23). Open the drain. Turn on the main supply and check for leaks. Open both hot and cold valves and run water through the spout to remove any debris. Turn the valve off. Reinstall the aerator.</p>
<h3>清洗说明</h3> <p>适用于所有加工处理过的表面：以中性肥皂水清洗镀层表面，再以干净的软布彻底擦干整个表面，有许多清洁剂，比如氨水、去污粉及洁厕灵等，会对电镀表面造成伤害，切忌使用。</p> <p>有磨损性的清洁用具或清洁剂也不可使用于科勒牌的水龙头及其配件上。</p>	<h3>CLEANING INSTRUCTIONS</h3> <p>All Finishes: Clean the finish with mild soap and warm water. Wipe entire surface completely dry with clean soft cloth. Many cleaners may contain chemicals, such as ammonia, chlorine, toilet cleaner etc. which could adversely affect the finish and are not recommended for cleaning.</p> <p>Do not use abrasive cleaners or solvents on Kohler faucets and fittings.</p>