STERLING
A KOHLER COMPANY

# Finesse™ Peak®

Frameless sliding shower door

**547808-59**

## Features

- Frameless.
- 5/16" (8 mm) thick tempered glass.

## Technology

- CleanCoat® nanotechnology provides a smooth, nonstick surface to help prevent buildup of water stains, bacteria and mildew on your glass, to make it easy to clean and keep it looking like new.
- Vertical blade handles complete the look of this door.
- Out-of-plumb adjustability.
- Tempered glass ensures maximum safety and durability.
- Stainless steel hardware prevents rusting and corrosion.

## Installation

- Not for use in hospitality.
- For residential use only.

## Recommended Products/Accessories

K-23723 Faucet cleaner

## Included Components

Additional Components:

Hardware kit

## Codes/Standards

ANSI Z97.1
CPSC 16CFR 1201

## STERLING® Bath and Shower Doors Five-Year Limited Warranty

See website for detailed warranty information.

## Available Colors/Finishes

*Color tiles intended for reference only.*

| Color | Code | Description |
|---|---|---|
| | DR | Deep Bronze |
| | N | Nickel |
| | PBL | Matte Black |
| | S | Silver |

# Finesse™ Peak®

Frameless sliding shower door

**547808-59**




* Walk-Through

## Technical Information

All product dimensions are nominal.

| | |
|---|---|
| Frame material: | Aluminum |
| Installation type: | For shower base installation |
| Opening style: | Sliding/Bypass |
| Opening Width - Min: | 54-5/8" (1387 mm) |
| Opening Width - Max: | 59-5/8" (1514 mm) |
| Walk-through - Min: | 21-3/4" (552 mm) |
| Walk-through - Max: | 26-3/4" (679 mm) |
| Base-To-Wall Radius – Max: | 5/8" (16 mm) |
| Glass thickness: | 5/16" (8 mm) |

## Notes

Install this product according to the installation guide.

NOTICE: The vertical opening should be a minimum of 72" (1829 mm) to allow clearance for installation.