

PLAIN BATH K-45702X

Features

- Acrylic and reinforced with fiberglass
- Drop-in
- Includes pop-up drain and overflow
- Includes white pillow head (K-45702X-ZZ)
- Molded armrests
- 1700 x 800 x 450 mm

Codes/Standards Applicable

Specified model meets or exceeds the following:

- ANSI Z124.1.2
- TIS 2141-2546



Technical Information

Fixture:	
Basin area:	
Basin area bottom	1240 x 560 mm
Basin area top	1600 x 700 mm
To overflow:	
Water depth	305 mm
Capacity	220 liters
Drain hole	ø38 mm (1-1/2")
Overflow hole	ø52 mm
Weight	25 kg
*Approximate measurements for comparison only.	

Installation Notes


Install this product according to the installation guide. Floor support under bath must provide for a minimum of 390 kg/square meter loading. This bath is designed for drop-in installation only.

Specified Model


Model	Description	Color/Finished
K-45702X	Duo 1700 plain bath	0: White
K-45702X-ZZ	Duo 1700 plain bath, white pillow	0: White

Dimensions are approximate.

Unit: mm



Minimum access panel bath drain W500 x H450 mm



Note: The recommended dimension for installation can be adjusted according to user preferences and layout.

Product Diagram

อ่างอาบน้ำน้ำ K-45702X



คุณลักษณะ

- อะคริลิกเสริมใยแก้ว
- แบบฝัง
- พร้อมตะตืออ่างแบบป๊อปอัพและท่อน้ำล้น
- พร้อมหมอนสีขา (K-45702X-ZZ)
- พร้อมที่พักแขนในตัว
- 1700 x 800 x 450 มม.

มาตรฐาน

- คุณสมบัติตามมาตรฐาน
- ANSI Z124.1.2
 - มอก. 2141-2546

ข้อมูลผลิตภัณฑ์

ข้อมูลอ่างอาบน้ำ:	
พื้นที่ด้านล่าง	1240 x 560 มม.
พื้นที่ด้านบน	1600 x 700 มม.
ถึงระดับน้ำล้น:	
ระดับน้ำลึก	305 มม.
ความจุน้ำ	220 ลิตร
ขนาดรูท่อน้ำทิ้ง	Ø38 มม. (1-1/2")
ขนาดรูน้ำล้น	Ø52 มม.
น้ำหนัก	25 กก.
*ระยะค่าประมาณสำหรับเพื่อเปรียบเทียบเท่านั้น	


ข้อสังเกตสำหรับการติดตั้ง

ติดตั้งผลิตภัณฑ์โดยใช้คู่มือข้อแนะนำการติดตั้ง
พื้นที่ใช้รองรับอ่างอาบน้ำต้องสามารถรับน้ำหนักอย่างน้อย 390 กก./ตร.ม.
อ่างอาบน้ำถูกออกแบบสำหรับการติดตั้งแบบฝังเท่านั้น



รุ่นผลิตภัณฑ์

รุ่น	ชื่อผลิตภัณฑ์	สี/วัสดุเคลือบผิว
K-45702X	อ่างอาบน้ำอะคริลิก รุ่นคูโอบั 1700	0: สีขาว
K-45702X-ZZ	อ่างอาบน้ำอะคริลิก รุ่นคูโอบั 1700 พร้อมหมอนสีขา	0: สีขาว

ขนาดระยะแสดงค่าโดยประมาณ
หน่วย: มม.



ช่องซ่อมบำรุงทางน้ำทิ้งมีขนาดอย่างน้อย กว้าง 500 x สูง 450 มม.



หมายเหตุ: ระยะแนะนำการติดตั้งสามารถปรับได้ตามความเหมาะสมของผู้ใช้งานและพื้นที่ติดตั้ง

ภาพแสดงผลิตภัณฑ์