KOHLER®

Strive®
Under-Mount Kitchen Sink
K-5409

Features
- 30-inch minimum base cabinet width.
- Single bowl.
- 9" depth provides generous workspace.
- No faucet holes.
- The increased dimensions of this sink maximize the space in a 30-inch base cabinet.
- Rear drain increases workspace in the sink and allows for more storage space underneath the sink.
- SilentShield® sound-absorption technology offers quieter performance.
- Includes the K-6429 dishcloth bar/utility shelf and the K-5408 bottom sink rack.
- Includes installation hardware.
- Rounded 10mm corners are easy to clean.

Material
- Handcrafted from 16-gauge stainless steel.
- Premium 16-gauge stainless steel.

Installation
- Undermount.

Recommended Products/Accessories
K-8801 Sink Strainer
K-8799 Sink Strainer
K-23726 Drain treatment
K-23729 Stainless steel cleaner

Optional Products/Accessories
K-11352 Disposal Flange with Stopper



Codes/Standards
ASME A112.19.3/CSA B45.4

Lifetime Limited Warranty for KOHLER® Stainless Steel Sinks
See website for detailed warranty information.

KOHLER®

Strive®

Under-Mount Kitchen Sink

K-5409



Technical Information

All product dimensions are nominal.

Bowl configuration:	Single
Installation:	Under-mount
Min. base cabinet width:	33" (838 mm)
Bowl area (Only):	Length: 27-1/4" (692 mm) Width: 16-9/16" (420 mm) Bowl depth: 9" (229 mm) Water depth: 9" (229 mm)
Template:	1220866-7, required, included

Notes

Install this product according to the installation instructions.

Minimum base cabinet width 30” - 33” (30” may require cabinet modifications). Consult an installer for confirmation.