

Features


- Elongated closed front seat fits most elongated toilets
- Continuously heated water with adjustable temperature settings
- 3 adjustable water pressure and oscillate functions
- Automatic nozzle clean with UV stabilizer
- Anti-microbial materials used in seat and nozzles
- Quick-Release functionality allows for ease of cleaning
- Includes power cord, 3 way connector and water supply hoses
- 530 x 430 x 120 mm

Codes/Standards Applicable

Specified model meets or exceeds the following:

- N/A

TOILET SEAT WITH BIDET FUNCTIONALITY K-22445X



Technical Information


Fixture:	
Water supply pressure	0.70-7.40 Bar (0.07-0.74 MPa)
Electrical rating	220 V, 50 Hz, 1100 W
Power cord length	About 1.5 m
Supply hose length	19" (48.3 cm)

Required Electrical Service

Dedicated circuit required, protected with Class A Ground-Fault Circuit-Interrupter (GFCI) or Earth Leakage Circuit Breaker (ELCB):	
Receptacle	220-240 V, 10 A, 50/60 Hz

Installation Notes

Install this product according to the installation guide.




ELECTRICAL SERVICE DETAIL

Specified Model

Model	Description	Color/Finished
K-22445X	C3-430 Smart seat	0: White

Dimensions are approximate.

Unit: mm



Note: The recommended dimension for installation can be adjusted according to user preferences and layout.

Product Diagram

คุณลักษณะ


- ฝารองนั่งปิดคลุมสำหรับโถสุขภัณฑ์แบบหน้ายาว
- ระบบทำน้ำอุ่นอย่างต่อเนื่องพร้อมระบบปรับอุณหภูมิ
- ก้านฉีดชำระสามารถปรับความแรงของน้ำ 3 ระดับ และฟังก์ชันฉีดพ่นหน้า-หลัง
- ระบบทำความสะอาดก้านฉีดชำระด้วยแสง UV
- ฝารองนั่งและหัวฉีดชำระทำจากวัสดุป้องกันแบคทีเรีย
- ฝารองนั่งแบบถอดออกง่ายเพื่อความสะดวกในการทำความสะอาด
- พร้อมสายไฟฟ้า ขั้วต่อสามทาง และสายน้ำดี
- 530 x 430 x 120 มม.

มาตรฐาน

คุณสมบัติตามมาตรฐาน

- ไม่ระบุ

ฝารองนั่งอเนกประสงค์ K-22445X



ข้อมูลผลิตภัณฑ์


สุขภัณฑ์	
แรงดันน้ำ	0.70-7.40 บาร์ (0.07-0.74 เมกะปาสคาล)
กำลังไฟ	220 โวลต์, 50 เฮิร์ตซ์, 1100 วัตต์
ความยาวสายไฟ	ประมาณ 1.5 เมตร
ความยาวสายน้ำดี	19" (48.3 เซนติเมตร)

ข้อกำหนดกระแสไฟฟ้า

ติดตั้งอุปกรณ์ตัดกระแสไฟฟ้าลัดวงจรแบบ GFCI (Ground-Fault Circuit-Interrupter) หรือ ELCB (Earth Leakage Circuit Breaker):	
ขนาด	220-240 โวลต์, 10 แอมป์, 50/60 เฮิร์ตซ์

ข้อสังเกตสำหรับการติดตั้ง


ติดตั้งสุขภัณฑ์โดยใช้คู่มือแนะนำการติดตั้ง



รุ่นผลิตภัณฑ์

รุ่น	ชื่อผลิตภัณฑ์	สี/วัสดุเคลือบผิว
K-22445X	ฝารองนั่งอเนกประสงค์ รุ่น C3-430	0: สีขาว

ขนาดระยะแสดงค่าโดยประมาณ
หน่วย: มม.



หมายเหตุ: ระยะแนะนำการติดตั้งสามารถปรับได้ตามความเหมาะสมของผู้ใช้งานและพื้นที่ติดตั้ง

ภาพแสดงผลิตภัณฑ์