

VANITY LAVATORY K-24369X

Features

- Fireclay
- Vanity top lavatory
- With overflow
- With flexible pipe
- With Washboard
- Single-hole
- 800 x 450 x 202 mm

Codes/Standards Applicable

Specified model meets or exceeds the following:

- ASME A112.19.2/CSA B45.1
- GB/T 6952



Technical Information

Fixture:	
Water depth	145 mm
Drain hole	45 mm D.
*Approximate measurements for comparison only.	

Installation Notes

Install this product according to instruction in the installation' guide
Spout must be a minimum 50 mm long for adequate clearance into lavatory.

IMPORTANT! Product rests on countertop. Account for height of product when designing installation.


Specified Model

Model	Description	Color/Finished
K-24369X-1	Maxispac 2.0, 800 mm vanity top	O: White

Required Accessory		
K-23799X	Maxispac 2.0 Bathroom cabinet 800 mm	MT9: Milk Tea

Dimensions are approximate.

Unit: mm



Note: The recommended dimension for installation can be adjusted according to user preferences and layout.

Product Diagram

อ่างล้างหน้าติดตั้งบนตู้เฟอร์นิเจอร์ K-24369X

คุณลักษณะ

- สุขภัณฑ์เซรามิกประเภทไฟร์เคลย์ (Fireclay)
- แบบติดตั้งบนตู้เฟอร์นิเจอร์
- พร้อมรูน้ำล้น
- พร้อมท่ออ่อน
- พร้อมกระดานชักผ้า
- แบบเจาะรูเดี่ยว
- 800 x 450 x 202 มม.

มาตรฐาน

- คุณสมบัติตามมาตรฐาน
- ASME A112.19.2/CSA B45.1
- GB/T 6952

ข้อมูลเฉพาะ

ผลิตภัณฑ์	
ระยะน้ำล้น	145 มม.
ขนาดรูสะดืออ่าง	เส้นผ่าศูนย์กลาง 45 มม.
*ระยะค่าประมาณสำหรับเพื่อเปรียบเทียบเท่านั้น	



ข้อสังเกตสำหรับการติดตั้ง

ติดตั้งผลิตภัณฑ์โดยใช้คู่มือข้อแนะนำการติดตั้ง เพื่อความเหมาะสมในการทำงานอ่างล้างหน้า ความยาวของปากก๊อกน้ำ ถึงขอบอ่างล้างหน้า ควรมีระยะไม่น้อยกว่า 50 มม.

ข้อสำคัญ! ค่าแนวระยะความสูงของสุขภัณฑ์ เมื่อสุขภัณฑ์วางอยู่บน เคาน์เตอร์


รุ่นผลิตภัณฑ์

รุ่น	ชื่อผลิตภัณฑ์	สี/วัสดุเคลือบผิว
K-24369X-1	อ่างล้างหน้าติดตั้งบนตู้เฟอร์นิเจอร์ รูเดี่ยว ขนาด 800 มม. รุ่นแม็กซีสเปซ	0: สีขาว

อุปกรณ์จำเป็น

K-23799X	ตู้เฟอร์นิเจอร์ ขนาด 800 มม. รุ่นแม็กซีสเปซ	MT9: ซีเมนต์กั๊ก
----------	---	------------------

ขนาดระยะแสดงค่าโดยประมาณ
หน่วย: มม.



หมายเหตุ: ระยะแนะนำการติดตั้งสามารถปรับได้ตามความเหมาะสมของผู้ใช้งานและพื้นที่ติดตั้ง

ภาพแสดงผลิตภัณฑ์