KOHLER® **INSTALLATION INSTRUCTIONS**

73061T-7 Single Handle Wall Mount Lavatory Faucet

BEFORE YOU BEGIN

All information is based on the latest product information available at the time of publication. Kohler Co. reserves the right to make changes in product characteristics, packaging, or availability at any time without notice.

Please leave these instructions for the consumer. They contain important information.


NOTES:

- 1. Flush the water supply pipes thoroughly to remove debris.
- 2. Inspect the supply tubing for damage. Replace as necessary.
- 3. Observe local plumbing codes.
- 4. Check for leaks before covering the pipes, repairs as needed.
- 5. Inlet threads of body are Rc1/2".

6. Please ensure only apply water pressure test on the product, and empty the air in pipe and faucet thoroughly before the test. Please ensure test pressure below 0.8MPa(8 bar) and test duration within 30 minutes.


HANDLE OPERATION

ROUGH-IN DIMENSIONS



COMPOSED

INSTALLATION




How to Install the Body

Determine where the valve body(1) will be located on the wall. Dig a suitable hole in the wall. Install the valve body into the hole. Be sure the protectors(2) face front and the inlet of the valve body with red mark is on the right.

NOTE: Ensure the centerline of valve is vertical to the wall, the up plane of valve body is horizontal.

Connect R1/2" hot and cold supplies to the inlets of the valve body. Connect hot supply to the right with red mark. Connect cold supply to the other inlet.

The out surface of the finished wall should be between the MAX and MIN marks on the protectors(2). During installation, the protectors remain on the valve body.




How to Install the Handle and Spout


Remove the protectors after the wall is finished.

Tighten the screws(4) with 3mm hex wrench(3) to secure the mounting plate(5) until it is against the wall.



Single Handle Wall Mount Lavatory Faucet 73061T-7






**Color code must be specified when ordering.

COMPOSED

7

INSTALLATION CHECKOUT



27

-28

29

Ensure that all coupling nuts are tight. Ensure that the handle is in the off position.

Turn on the main water supply and drain, and check for leaks. Repair as needed.

Remove the aerator(24) by key(23). Run hot and cold water through faucet for about one minute to remove any debris.

Remove any debris from the aerator. Shut off the faucet. Reinstall the aerator.

Replacing the Washer and Piston Kit


Turn counter clockwise to remove the stopper(27). Take out washer(28). Replace with a new one.


Turn counter clockwise to remove the piston kit(29). Replace with a new one. Reinstall stopper and washer.


CLEANING INSTRUCTIONS


All Finishes: Clean the finish with mild soap and warm water. Wipe entire surface completely dry with clean soft cloth. Many cleaners may contain chemicals, such as ammonia, chlorine, toilet cleaner etc, which could adversely affect the finish and are not recommended for cleaning.

Do not use abrasive cleaners or solvents on Kohler faucets and fittings.









How to Install the Drain

Remove the locknut(21), plastic washer(20) and the rubber gasket(19) and tailpiece(24) from the drain body.

Supply enough tape or sealant to tailpiece thread. Reinstall the tailpiece.

Insert the drain body into the lavatory. Install the rubber gasket(Tapered side up), plastic washer and locknut back to the drain body in turn. Tighten the locknut.

NOTE: If needed, apply a ring of plumbers putty or other sealants around the underside of the drain flange(22), instead of using rubber washer(23).

Do not reposition the drain after the locknut is tightened, or you may break the putty or sealant seal. Remove any excess putty.

(7)