

TWO-PIECE TOILET WITH SEAT K-28417X-S


Features

- Vitreous china.
- Elongated bowl.
- Includes Quiet close seat.
- Includes polished chrome push button.
- Wash Down flushing system
- Dual flush 3/4.5 liter per flush
- 185 mm rough-in for Plastic P-trap
- 700 x 391 x 776 mm

Codes/Standards Applicable

Specified model meets or exceeds the following:

- TIS 792



Technical Information

Fixture:	
Configuration	two-piece, elongated
Water per flush	3/4.5 liter
Passageway	51 mm
Water area	127 x 102 mm
Water depth from rim	240 mm
Seat post hole centers	140 mm

Included Components:	
Bowl	F28412-**
Tank	F22243-BWA1-**
Tank cover	1203722-SP-**
Quiet close seat	K-3857K-**
Plastic P-Trap	1138552

Installation Notes

Install this product according to the installation guide.


Specified Model

Model	Description	Color/Finishes
K-28417X-S	Reach Concealed two-piece toilet, P-trap with Quiet close seat	0: White

Dimensions are approximate. (Do not direct measure a dimensional from picture below)

Unit: mm


This diagram show with K-3857K seat



Note: The recommended dimension for installation can be adjusted according to user preferences and layout.

Product Diagram

สุขภัณฑ์สองชิ้นพร้อมฝารองนั่ง K-28417X-S



คุณลักษณะ

- สุขภัณฑ์เซรามิกประเภทวีเทรียสไชน่า (Vitreous china)
- โถสุขภัณฑ์แบบหน้ายาว
- พร้อมฝารองนั่งแบบกันกระแทก
- พร้อมปุ่มกดชำระสีโครมเงา
- ระบบชำระล้างแบบวอลูตาดาร์น
- ใช้น้ำในการชำระล้าง 3/4.5 ลิตร
- ระยะจุดกึ่งกลางท่อน้ำทิ้งถึงผนัง 185 มม. สำหรับการติดตั้งท่อน้ำทิ้งออกผนัง
- 700 x 391 x 776 มม.

มาตรฐาน

- คุณสมบัติตามมาตรฐาน
- มอก. 792

ข้อมูลเฉพาะ

สุขภัณฑ์	
ลักษณะ	สุขภัณฑ์สองชิ้น, หน้ายาว
การใช้น้ำชำระล้างต่อครั้ง	3/4.5 ลิตร
ขนาดท่อน้ำทิ้ง	51 มม.
ผิวหน้า	127 x 102 มม.
ความลึกจากขอบโถสุขภัณฑ์ถึงผิวหน้า	240 มม.
ระยะห่างระหว่างรูยึดฝารองนั่ง	140 มม.

ส่วนประกอบสุขภัณฑ์	
โถสุขภัณฑ์	F28412-**
ถังพักน้ำ	F22243-BWA1-**
ฝาปิดถังพักน้ำ	1203722-SP-**
ฝารองนั่งแบบกันกระแทก	K-3857K-**
ท่อน้ำทิ้งแบบออกผนัง	1138552

ข้อสังเกตสำหรับการติดตั้ง


ติดตั้งสุขภัณฑ์โดยใช้คู่มือแนะนำการติดตั้ง

รุ่นผลิตภัณฑ์

รุ่น	ชื่อผลิตภัณฑ์	สี/วัสดุเคลือบผิว
K-28417X-S	สุขภัณฑ์สองชิ้น แบบท่อน้ำทิ้งออกผนัง รุ่น วีซี คอนเซ็ล พร้อมฝารองนั่งแบบกันกระแทก	0 : สีขาว

ขนาดระยะแสดงค่าโดยประมาณ (ห้ามวัดขนาดโดยตรงจากภาพด้านล่าง)
หน่วย: มม.

ภาพแสดงผลิตภัณฑ์พร้อมฝารองนั่ง K-3857K



หมายเหตุ: ระยะแนะนำการติดตั้งสามารถปรับได้ตามความเหมาะสมของผู้ใช้งานและพื้นที่ติดตั้ง

ภาพแสดงผลิตภัณฑ์