

BEFORE YOU BEGIN

Observe all local plumbing and building codes. Prior to installation, unpack the new lavatory and inspect it for damage. Return the lavatory to its protective carton until you are ready to install it.

These instructions are for installing the lavatory to wood frame construction. For other installation, supply suitable bracing and fastening devices of sufficient size and strength.

The walls and floor must be square, plumb, and level.

- Kohler lavatory is made according to American National Standard that it can match the American lavatory fittings. Any other lavatory fittings may not fit for Kohler lavatory.

安装之前

遵守当地所有给排水和建筑规定。

安装之前先开启新脸盆的包装，检查有无破损后放回纸箱中以免碰坏，到准备安装时才取用。

以下安装指引适用于安装脸盆于木框结构之中，其他的结构需另置合适尺寸和强度的支撑及紧固装设配套。

墙壁和地板必须方正、平整和水平。

- 科勒洗脸盆是根据美国标准制造的，与美式洗脸盆配件相配。其它洗脸盆配件可能与之不相配。

ROUGHING-IN

(S) Supply 254mm (10") (Based on 305mm (12") riser which may require cutting).

(T) Pop-up drain typically 330mm (13").


Fixture dimensions are nominal and conform to tolerances in ASME Standard A112.19.2M.

尺寸图

(S) 254mm 供水管(根据305mm 冒口而定，可能需切短)

(T) 凸出排水管一般为330mm。

部件尺寸为标定值，误差符合美国机械工程师学会(ASME)标准A112.19.2M。



广东省佛山市三水区乐平镇第二工业区
佛山科勒有限公司 邮编: 528137

TOOLS AND MATERIALS REQUIRED (Not Supplied)

- Level
- Drill with assorted bits
- Socket wrench with 203mm (8") extension & assorted sockets
- Tape measure
- Framing square
- Channel lock pliers
- 14mm(9/16") wrench
- Bolts (6) and washers (6) to secure hanger to wall
- Screw and washer to secure pedestal to floor

Note: Materials required may differ depending on type of substrate.

所需工具及材料 (不随货供应)

- 水平尺
- 带配套钻头的钻
- 接头板钳附有203mm把手及接头配套
- 卷尺
- 定位直尺
- 锁钳
- 14mm板钳
- 在墙上安装悬挂架用的螺栓(6枚)及垫圈(6枚)
- 在地面固定立柱用的螺栓及垫圈

注意: 需要视乎墙壁或地面的用料而使用不同的螺栓及垫圈。

ACCESSORIES INCLUDED WITH PRODUCT

63069 Leveling Pads
52204 Accessories Pack
64839 Hanger

Additional accessories other than those provided may be required for installation.

随货供应的配件

63069 水平垫
52204 安装组件
64839 悬挂架

安装时或需要不随货供应之额外配件。


INSTALLATION

安装

- Rough-in the supplies and the drain piping and trap.

NOTE: The supply stop handles cannot extend more than 95mm (3-3/4") from the finished wall when in the open position.

- Install sufficient backing behind the finish wall to provide a secure material for the anchoring devices.
- Install hanger to wall according to roughing-in dimensions. For masonry applications, use suitable anchors.



画出供水管排水管道及弯管的坑距。

注意: 供水开关手柄在旋开位置时，距离完工墙面不得超过95mm。

- 要在完工的墙后安装足够的支撑，为锚固装置提供牢靠的基础。
- 按照坑距尺寸把悬挂架安装在墙上。若需安装在水泥上，请用合适的塞子。


NOTE: To avoid damage to pedestal or floor, slide cardboard under pedestal before moving.

- Mark the centerline on the floor.
- Position the pedestal on the floor centerline so the mounting hole is approximately 165mm (6-1/2") from the finished wall.
- Position the lavatory on the hanger and pedestal.
- Move the pedestal as required to ensure proper fit in the desired location.

NOTE: The lavatory **must** be supported by the hanger **and** pedestal.

- Check the lavatory placement.
- Mark the center of each anchoring hole on the wall, and mark the floor through the hole in the pedestal bottom.
- Carefully remove the lavatory from the pedestal. Then move the pedestal from the area.

Finished Wall
完工墙




注意: 为避免弄坏立柱或地面, 移动立柱前先在下面垫上薄纸板。

- 在地面上画出中心线标记。
- 把立柱放在地面中心线位置上, 离完工墙约165mm。
- 将脸盆安放在悬挂架及立柱上。
- 必要时移动立柱, 以确保位置恰当。

注意: 脸盆**必须**由悬挂架及立柱支撑。


- 检查脸盆是否安放正确。
- 在墙上标出每个锚孔的中心位置, 并通过立柱底部的孔, 在地面上作出标记。
- 小心地从立柱上移开脸盆, 再将立柱搬开。

- Drill mounting holes at the marks on the floor and wall.



- 在地面及墙上标记处钻上安装孔。

- Install the faucet and drain to the lavatory according to the manufacturer's instructions.




- 按照制造商之指引, 将水龙头及排水管道安装在脸盆上。

NOTE: Do not fully tighten slip-joint drain connection at this time.

注意: 此时勿将滑动排水连接器完全上紧。

- Position the pedestal mounting hole over the hole in the floor.
- Secure the pedestal to the floor with the screw and washer. Tighten the screw until it is snug. For masonry applications, use suitable anchor.



- 把立柱安装孔对准地面的孔。
- 用螺钉及垫圈将立柱固定在地面上, 上紧螺钉直至贴合为止。若需安装在水泥地上, 请用合适的塞子。

CAUTION: Risk of product damage. Do not overtighten. Overtightening may cause damage to the product.

小心: 有产品损坏之危险。 螺钉不要上得过紧, 否则可能损坏产品。


- Set the lavatory on the hanger and pedestal, and level the lavatory using leveling pads.

- secure the lavatory to the wall with bolts and washers.



CAUTION: Risk of product damage. Do not overtighten bolts nuts. Overtightening may cause damage to the product.

- Connect and tighten the trap to drain.
Connect the hot and cold water supplies to the faucet.



- 将脸盆放于悬挂架及立柱上，用水平垫调平脸盆。

- 用螺栓及垫圈将脸盆固定在墙上。



小心：有产品损坏之危险。不要把螺栓上得过紧，否则可能损坏产品。

- 把弯管联接排水管并上紧，同时将热水及冷水管接上水龙头。

IMPORTANT CONSUMER INFORMATION

用户须知

CARE AND CLEANING

To keep your lavatory looking new, make sure you rinse it out thoroughly after each use. **DO NOT ABRASIVES** on this product, as they will scratch and ruin the surface. Stubborn stains, paint, or tar can be removed with turpentine or paint thinner.

护理和清洁

为保持脸盆常新，请确保每次使用后立即彻底冲洗，**但切勿用腐蚀性清洁剂**，以防止刮花或磨损盆面。如有顽渍、油漆或柏油点，可用松油或油漆稀释剂清洗。

LIMITED ONE-YEAR WARRANTY

一年有限担保

Plumbing Fixtures and Fittings Limited One-year Warranty

陶瓷及浴缸产品及配件担保——一年有限担保

Kohler plumbing fixtures and fittings are warranted to be free of manufacturing defects.

科勒公司担保其陶瓷及浴缸产品及配件在制造工艺上无瑕疵。

This product is warranted for one year from date of purchase. Kohler China will be responsible for any problems caused by manufacturing defects provided with the invoice. Kohler China will, at its election, repair, replace or make appropriate adjustment where Kohler China inspection discloses any such defects occurring in normal usage within one year after purchase.

本产品自购买之日起即获得本公司一年的质量保证。在质保期内，凭购货发票，科勒公司将免费承担由制造质量引起的任何问题。经核查后，科勒中国有限公司有权决定是修理、更换、还是作适当的调整。

Implied warranties including that of merchantability and fitness for a particular purpose are expressly limited in duration to the duration of this warranty, Kohler China disclaims any liability for special, incidental or consequential damages. Damages to the product caused by misuse, abuse and installation that is not in accordance with the owner's manual are not covered by this warranty.

这里所指的担保，包括产品，都已明确地限制在该担保期之内。科勒中国有限公司对其后出现的损坏不负有任何责任。担保也不包括外观损伤、使用不当以及未按说明书安装的损失。

To obtain quick warranty service, please contact your dealer, or write to Kohler China. (Original sales receipt must be provided as the proof of purchase.)

为获得快捷的担保服务，请联系您的销售商；您也可写信给科勒中国有限公司(请出示销售发票原件作为购货凭证)：

Kohler China Investment Company Ltd.
Central Customer Service Center
19/F, Shanghai Square, 138 Huai Hai Road,
Luwan District, Shanghai, PRC
Zip Code: 200021

科勒(中国)投资有限公司
中央客户服务中心
上海市卢湾区淮海中路138号
上海广场19楼
邮编：200021

This is our exclusive written warranty.

这是我们全部的书面担保。