


K-2479T 帕蒂欧时尚脸盆 PATIO VESSEL

釉面陶瓷台上式脸盆 ABOVE-THE-COUNTER VITREOUS CHINA LAVATORY 切割图 / 安装说明书 CUT-OUT TEMPLATE / INSTALLATION INSTRUCTION



当按实际大小绘制切割图时, 请确定脸盆水平及垂直方向的大小跟切割图上所标注的尺寸是一致的。
WHEN PLOTTING TEMPLATE FULL SIZE:
Make sure horizontal and vertical dimensions match the dimensions labeled on the template.

沿此线切割
CUT ALONG THIS LINE



盆边缘
RIM OF LAVATORY

尺寸图



ROUGH-IN




Fig. #1
图1

尺寸资料

产品尺寸均为标准值, 误差均符合美国机械工程协会(ASME)112.19.2M标准。

(T) 使用提拉杆去水头238mm。

(S) 356mm; 此尺寸根据305mm缸口计算, 须按实际情况调整。

* 采用图示中心线安装时, 龙头出水嘴须127mm长(最少)以保持其伸入脸盆的距离。

** 出水嘴颈高达78mm并根据ASME A112.1.2标准, 有25mm气隙。

Roughing-In Notes

Fixture dimensions are nominal and conform to tolerances in ASME Standard A112.19.2M.

(T) Pop-up drain 238mm.

(S) 356mm (Based on 305mm riser which may require cutting).

* Spout must be 127mm long (min.) for adequate clearance into lavatory when installed

** Spout must be tall enough to clear 76mm rim height and provide a 25mm air gap per

安装之前

- 台上式脸盆可使用此说明书, 请遵照适合您安装需要的说明进行。
- 根据您所需的安装地及安装风格, 你可选择说龙头靠墙安装或台上式安装。建议您采用靠墙式龙头。
- 安装之前, 先打开脸盆的包装, 并小心检查新的脸盆是否有损坏, 再将脸盆放回包装盒内, 到安装时才取用。
- 本说明书所含一切资料, 均以印刷时所有的最新产品为准。科勒公司保留随时更改产品特性, 包装或供货情况的权利, 恕不另行通知。
- 此说明书包括重要的护理, 清洁及保修资料, 请务必仔细阅读并保留。
- 科勒脸盆是根据美国标准制造的, 与美国式洗脸盆配件相配。其它洗脸盆配件可能与之不相配。

所需工具及材料 (不随货供应)

- 密封胶
- 安装模板(已提供)
- 安全眼罩
- 炭笔
- 剪刀
- 卷尺
- 孔锯
- 匙孔锯或军刀状锯
- 电钻(直径为13mm的钻嘴或更大的钻嘴)
- 螺丝刀

安装台面

将模板放在台面上。

安装靠墙式水龙头: 保证出水嘴悬于脸盆池上有足够的距离。需要出水嘴的最小长度资料, 可参阅尺寸说明。

安装台上式水龙头: 安放水龙头时, 要如下列提示一样, 特别注意出水嘴与把手的配合间隙。利用模板将水龙头出水嘴中心线放在台板上, 建议中心线在脸盆边缘与出水嘴间留有足够的距离。

检查防溅木板或后端, 水龙头出水嘴与把手之间是否有足够的间隙。我们建议至少留 25mm 的间隙, 在:

- 安好的脸盆与水龙头出水嘴之间
 - 安放的脸盆与把手末端之间
 - 水龙头出水嘴、把手与防溅木板或后端之间
- 注意:** 在中国一般不单靠墙安装防溅木板, 安装台盆的后端即为“防溅木板”。
- 请务必了解所需问题, 请参阅水龙头安装说明书, 并用一软性铅笔标出要安装水龙头的孔的位置。

用一软性铅笔在台面上沿模板画线。

仔细地沿软性铅笔切割开口。

小心: 提防身体受伤或损坏产品。 大型脸盆相当重, 须请人帮忙一起搬动及安放。

暂将脸盆放入台面切口的位置, 能看见“Kohler”字样。此字样应位于脸盆池内, 靠近盆池, 接近水龙头的地方。

检查脸盆、水龙头及防溅木板或后端之间的间距是否适当。

将脸盆从台面切口处移开并将其放入起保护作用纸箱中, 不可将脸盆竖立放置或将排水一倒放在地上。

钻好水龙头口。

依照制造商的说明书, 将水龙头安装在台面上。

依照附在排水装置中的说明书, 将排水装置安装在脸盆上。安装排水装置时, 请使用足够的清澈型密封胶。

BEFORE YOU BEGIN

- Use these instructions for above-counter installation. Please follow the instructions that apply to your installation.
- You can choose between a wall-mount or countertop faucet installation, depending upon the setting and styling you desire. We recommended a wall-mount faucet.
- Prior to installation, unpack the new lavatory and carefully inspect it for damage. Return the lavatory to its protective carton until you are ready to install it.
- All information in these instructions is based upon the latest product information available at the time of publication. Kohler China reserves the right to make changes in product characteristics, packaging, or availability at any time without notice.
- These instructions contain import care, cleaning, and warranty information please leave these instructions for the consumer.
- Kohler lavatory is made according to American National Standard that it can match the American lavatory fittings. Any other lavatory fittings may not fit for Kohler lavatory.

TOOLS AND MATERIALS REQUIRED (NOT SUPPLIED)

- Sealant
- Template (supplied)
- Safety glasses
- Pencil
- Scissors
- Tape Measure
- Hole Saw
- Keyhole saw or saber saw
- Drill (1/2" dia. Drill bit, or larger)
- Screwdriver

COUNTERTOP INSTALLATIONS

Position the template on the countertop.

For Wall-mount faucets: Be sure to provide sufficient spout overhang into the lavatory basin. See the roughing-in notes for minimum spout length information.

For Countertop Faucets: Pay special attention to the spout and handle fit clearance when locating the faucet, as noted below. Use the template to locate the faucet spout hole centerline on the countertop. This centerline is recommended to provide adequate clearance between the edge of the lavatory and the spout.

Check for adequate clearance between the backsplash or wall faucet spout and handles, and lavatory. We recommend clearance of at least 25mm between:

- The installed lavatory and the faucet spout.
 - The installed lavatory and the end of the faucet handles, and
 - The faucet spout and handles and the backsplash or wall.
- NOTE:** In china installation will not have separate backsplash. The back wall is the "backsplash". Refer to the faucet installation instructions for required clearance, and mark the preferred faucet hole locations using a soft lead pencil.

Trace the template on the countertop using a soft lead pencil. Cut out the opening by carefully following the pencil line.

CAUTION: Risk of personal injury or product damage. Large lavatories are very heavy. Get help lifting the lavatory into place.

Temporarily position the lavatory in the countertop cutout so the "Kohler" logo is visible. The logo is located inside the basin, near the rim, and should be positioned near the faucet.

Verify proper clearance between the lavatory, faucet, and backsplash.

Remove the lavatory from the countertop cutout, and return it to its protective carton. Do not stand or store the lavatory on the drain surface.

Drill the faucet holes.

Install the faucet to the countertop according to the manufacturer's instructions.

Install the drain to the lavatory according to the installation instructions included with the drain. Apply a sufficient amount of clear silicone sealant when you install the drain.

对于瓷砖、木材或其它多孔材料, 请使用防水密封胶涂在台面的切口处, 遵守制造商提供的一切说明及警告。待密封胶干后, 方可进行安装。

请使用50/50异丙醇与水的混合物来清洁切口周围的台面, 用一干净抹布擦干。

注意: 当温度至少为10°C时, 才可使用密封胶, 使用密封胶的最佳温度范围为21°C至38°C。

将密封胶轻轻地涂在台面前口的四周, 使其覆盖在切口割上。在拆除支撑材料前, 请调整一下密封胶涂抹的地方, 擦去多余的密封胶。仔细地将其支撑密封胶的材料移开。

小心: 提防身体受伤或损坏产品。 大型脸盆相当重, 须请人帮忙一起搬动及安放。

注意“Kohler”字样的位置, 脸盆安装完毕后, 应能看见此字样。

小心地将脸盆放入台面切口适当位置, 向下按平。

联接水龙头供水管。

联接排水装置。

开启水龙头阀门, 检查有无渗漏。

用非腐蚀性清洁剂来清洁。

注意: 采用此切割模板切割的台面沿到面盆内边缘的距离为6mm左右, 客户可根据需要按比例缩放用以切割台面。

用户须知 (护理和清洁)

为保持脸盆光洁如新, 须确保每次使用后彻底冲洗干净, 切勿使用腐蚀性的清洁剂, 以免刮花及破坏脸盆的表面。要清除顽固污垢、油漆或柏油, 可使用松油或油漆稀释剂。

陶瓷及浴缸产品及配件担保——一年有限担保

科勒公司担保其陶瓷及浴缸产品及配件在制造工艺上无瑕疵。

本产品自购买之日起即获得本公司一年的质量担保。在质保期内, 凭购货发票, 科勒公司将免费承担由制造质量问题引起的任何问题。经检查后, 科勒中国有限公司有权决定是修理、更换, 还是适当的调整。

这里所指的担保, 包括产品, 都已明确地限制在该担保期之内。科勒中国有限公司对其后出现的损坏不负有任何责任。担保也不包括外观损伤、使用不当以及未按说明书安装的损失。

为获得快捷的担保服务, 请联系您的销售商; 您也可写信给科勒中国有限公司(请出示销售发票原件作为购货凭证):

科勒(中国)投资有限公司
中央客户服务中心
上海市卢湾区淮海中路138号
上海广场19楼
邮编: 200021

这是我们全部的书面担保。

To obtain quick warranty service, please contact your dealer, or write to Kohler China. (Original sales receipt must be provided as the proof of purchase.)

This is our exclusive written warranty.

For tile, wood, or other porous materials, apply waterproof sealant around the cutout area of the countertop surface. Follow all manufacturer's instructions and warnings. Allow the sealant to dry before proceeding. Use a 50/50 mixture of isopropyl alcohol and water to clean the countertop surface around the cutout area. Wipe dry with a clean cloth.

NOTE: Install the adhesive sealant when the temperature is at least 10°C. The preferred temperature range to apply the adhesive sealant is 21°C to 38°C. Loosely apply the adhesive sealant around the entire countertop cutout so it is alongside the cutout hole. Adjust the placement of the sealant before removing the backing material. Cut off any excess seal material. Carefully remove the adhesive seal backing material.

将密封胶轻轻地涂在台面前口的四周, 使其覆盖在切口割上。在拆除支撑材料前, 请调整一下密封胶涂抹的地方, 擦去多余的密封胶。仔细地将其支撑密封胶的材料移开。

CAUTION: Risk of personal injury or product damage. Large lavatories are very heavy. Get help lifting the lavatory into place.

Note the location of the "Kohler" logo. The lavatory should be installed so the logo is visible after installation.

Carefully position the lavatory in the cutout, and press down firmly.

Connect the faucet supply lines.

Connect the drain assembly.

Open the faucet valves, and check for leakage.

Clean up with a non-abrasive cleaner.

NOTE: Using this template, the overhang is about 6mm. Customers can zoom the template by scale to meet their requirement.

IMPORTANT CONSUMER INFORMATION (CARE AND CLEANING)

To keep your lavatory looking new, make sure you rinse it out thoroughly after each use. **DO NOT USE ABRASIVES** on this product, as they will scratch and ruin the surface. Stubborn stains, paint, or tar can be removed with turpentine or paint thinner.

Plumbing Fixtures and Fittings Limited One-year Warranty

Kohler plumbing fixtures and fittings are warranted to be free of manufacturing defects.

This product is warranted for one year from date of purchase. Kohler China will be responsible for any problems caused by manufacturing defects provided with the invoice. Kohler China will, at its election, repair, replace or make appropriate adjustment where Kohler China inspection discloses any such defects occurring in normal usage within one year after purchase.

Implied warranties including that of merchantability and fitness for a particular purpose are expressly limited in duration to the duration of this warranty. Kohler China disclaims any liability for special, incidental or consequential damages. Damages to the product caused by misuse, abuse and installation that is not in accordance with the owner's manual are not covered by this warranty.

To obtain quick warranty service, please contact your dealer, or write to Kohler China. (Original sales receipt must be provided as the proof of purchase.)

Kohler (China) Investment Company Ltd.
Central Customer Service Center
19/F, Shanghai Square, 138 Huai Hai Road,
Luwán District, Shanghai, PRC
Zip Code: 200021

This is our exclusive written warranty.