KOHLER®
科勒®厨卫经典

安琪儿 CHALKSTRIPE
艾珀 ALBERRY

安装说明书
INSTALLATION INSTRUCTIONS
镜子
MIRRORS
K-2508T/K-2503T

BEFORE YOU BEGIN

- Please read these instructions carefully to familiarize yourself with the required tools, materials, and installation sequences. Follow the sections that pertain to your particular installation . This will help you avoid costly mistakes. In addition to proper installation, read all operating and safety instructions.
- All information in these instructions is based upon the latest product information available at the time of publication. Kohler China Ltd. reserves the right to make changes in product characteristics, packaging, or availability at any time without notice.
- These instructions contain important care, cleaning, and warranty information-**please leave instructions for the consumer.**
- Obey all electrical regulations in force at the time of installation.
- The mirror adopts top-grak birch and is processed with delicate technic.

⚠ **Warning! Risk of personal injury and product damage.** Mirrored cabinets are very heavy and should not be lifted or installed by just one person.

安装之前

- 请仔细详阅本指引，以便熟悉所需工具、物料及安装程序。请遵照适用的章节来安装本产品，以免安装失当导致不必要的损失。除了有关正确的安装方法之外，还务请详阅所有操作及安全指引。
- 本指引所载之一切资料，均以印刷时所有之最新产品情况为基础，科勒中国保留权利随时更改产品特性、包装或供应情况，恕不另行通知。
- 本指引也包含了有关保养、清洁及担保等重要资料-**请交予用户保存。**
- 遵循当地所有的电器安装规定。
- 该镜子采用优质桦木实木材精心加工而成。

⚠ **警告！小心人身伤害和产品受损**。镜架安装时请勿一人操作。

ORDERING INFORMATION

This installation covers the following products in the CHALKSTRIPE range:

CHALKSTRIPE Mirror.....K-2508T

This installation covers the following products in the ALBERRY range:

ALBERRY Mirror.....K-2503T

订购信息

此安装说明书适用于以下安琪儿系列家具的安装：

安琪儿镜子.....K-2508T

此安装说明书适用于以下艾珀系列家具的安装：

艾珀镜子.....K-2503T

SAFETY: WARNINGS

Kohler products are precision engineered and should give continued superior and safe performance, provided:

1.They are installed, commissioned, operated and maintained in accordance with the recommendations given in this Manual.

2.Periodic attention is given, as necessary, to maintain the product in good functional order. Recommended guidelines are given in the **MAINTENANCE** section.

Carefully inspect the new fixture for any signs of damage. When installing Kohler Products, manufacturers guidelines for power tool safety should be followed.

安全：警告

科勒产品经过精确制造，性能卓越，经久耐用。为保证产品品质，您必须：

1. 按照此手册中推荐的方法进行安装、起动、操作及维护。

2. 如有需要，定期检查，令产品保持良好性能状态。日常维护章节中列有推荐方法。

仔细检查新产品是否有损伤。
在安装科勒产品时，必须遵循制造商有关电动工具的安全指令。

科勒(中国)投资有限公司
上海市闸北区江场三路158号 邮编：200436

ⓒ版权为科勒中国有限公司所有，2008
ⓒCopyright Kohler China Ltd., 2008

ROUGHING-IN 尺寸图

UNIT : mm
单位：毫米

K-2508T











K-2503T


32
546
32
Silver mirror width 520
银镜宽 520


610
102
685
51
838
51
508
51
25
Silver mirror length 745.5
银镜长 745.5

INSTALLATION

安装步骤

1. Preparing the wall

a. Measure and mark 305mm center width.
b. Set mirror aside.

1. 墙面准备

a. 先用量具量出305mm的中心宽度，并标记。
b. 设定镜子安装边框



2. Measure and mark 108mm down from centre width mark

2. 在中心宽度标记下方量出距离标记位置108mm的长度，并标记。



3. Drilling holes

a. Drill holes for fixing hanged bracket and lay wall plug into the wall at the marked place. Using level to make sure that the hanged bracket is level.
b. Align center of hanger with marked point tapered side against wall.
c. Drill through studs at pilot holes locations.

3. 钻孔

a. 在墙上标记位置钻好挂墙式支架的安装孔，并插入入墙胶塞。使用水平仪检查，确保挂墙式支架水平。

b. 将挂墙式支架放在相应的标记位置上，边缘使用锥形夹固定。
c. 使用钻头在挂墙支架导向孔位置上钻孔。



4. Securing

a. Secure the hanged bracket on the wall with wall plug and screws.
b. Hang the pre-installed mirror hangers to the hanged bracket, and interlock hangers to mount mirror.

4. 固定

a. 使用入墙胶塞和螺丝完全固定住挂墙支架。

b. 将镜子预安装的背板挂在挂墙支架上，两者互锁，完全固定镜子。





USER MAINTENANCE

Warn! Risk of product damage.

1. Many cleansers contain abrasive and chemical substance which is not suitable for cleaning stainless steel, enamel, plating or plastic products. You may use mild cleansers or soaps to clean the surfaces. Wipe any splashes of cleaner solutions from the surface with clean soft cloth.

2. Maintain ventilation in the bathroom, and separate the dry area from the damp one if conditions permit. Try to open the door and windows of the bathroom and maintain good ventilation.

3. Kohler bathroom cabinet are dealt with strict procedures for damp-proof, whose good damp-proof function ensures good performance even in bathroom of huge humidity. Yet do not splash and pour water directly on the bathroom cabinet. Make sure that the bathroom is not over damp and wipe any splashes from surfaces immediately.

4. Maintenance of door board: Clean and wipe door board regularly, and wipe the condensation vapor with dry and soft cloth.

5. Ensure that electrical connections for appliances such as head lamp is insulated ; wipe mirror surface with chamois regularly to guarantee the persistent excellent performance.

6. Please do not sit, lean or step on the cabinet.

7. If any fixtures caused by abnormal reasons, Kohler China can supply paid replacement for service parts caused by abnormal reasons as shown in the next page in the limited duration of warranty.

日常维护

警告！小心产品受损。

1. 许多清洁剂都含有研磨剂及化学物质，不可用于清洁不锈钢、搪瓷、镀层或塑料制品。这些表面须使用温和的清洁剂或皂液进行清洁，将残余洗涤剂洗干净，然后用干净的软布擦干。

2. 卫生间请保持良好的通风状态，有条件的可以干、湿分离，平常尽量保持浴室空气畅通，养成开窗开门的习惯。

3. 科勒浴柜都经过严格的防潮处理，其良好的防潮性能可以保证在相对湿度很大的浴室里有良好的使用性，但使用时仍然不可以随意任浴柜被水浇、溅。所以请避免卫生间过于潮湿，遇有水迹要及时擦干。

4. 门板的保养：经常定期清洁、擦拭，洗浴后的冷凝水蒸气应用干燥的软干布擦净，保持门板的干爽

5. 照明灯电器连接要确保绝缘、防潮；镜面最好用麂皮经常擦拭，可以保障使用质量经久如一。

6. 请勿坐、倚靠、踩踏在浴柜上。

7. 科勒公司确保在担保期内，可以提供因非正常原因造成的如下页中零件的有偿更换。