

8588T-4

入墙式面板

8589T-4

入墙式切换面板

安装之前	BEFORE YOU BEGIN
<p>所有的资料是按最新出版的产品资料编写而成。科勒公司保留任何时候不经通知即可改变产品特性、包装或产品可供类型的权利。</p> <p>说明书包括重要的安装、保养及清洁方面的内容，请把这些资料交给用户阅读。</p> <p>注意事项：</p> <p>1. 一定要先彻底冲洗供水管以清除管道中的杂质。</p> <p>2. 在说明书所指示的恰当的时候，拿掉阀芯保护套。</p> <p>3. 参照 8588T-4 安装尺寸安装阀体 880T，参照 8589T-4 安装尺寸安装阀体 882T。</p>	<p>All information is based on the latest product information available at the time of publication. Kohler Co. reserves the right to make changes in product characteristics, packaging, or availability at any time without notice.</p> <p>Please leave these instructions for the consumer. They contain important information.</p> <p>Notes:</p> <p>1. Flush the water supply pipes throughly to remove debris.</p> <p>2. Do not remove the plaster guard from the valve body until instructed to.</p> <p>3. Install valve 880T according to the rough-in dimensions of 8588T-4. Install valve 882T according to the tough-in dimensions of 8589T-4.</p>
安装尺寸	ROUGH-IN DIMENSIONS
<div><div>8588T-4</div><div><p>装修好的墙面 The finished wall</p></div></div>	<div><div>8589T-4</div><div><p>装修好的墙面 The finished wall</p></div></div>



安装步骤

注意: 参照8588T-4安装尺寸安装阀体880T, 参照8589T-4安装尺寸安装阀体882T。

墙面装修好后, 拿掉保护套(1)。

将安装盘组件(4)套入阀体(3), 凸起(13)朝外(**注意:** 勿将环12、14挤出), 将其后推, 直至与墙面接触。用螺钉(2, 长50mm)固定安装盘组件。将面板(5)套在阀体上, 使开槽(6)向下。将其后推, 直至与墙面接触。将装饰盖(7)旋到阀体上。

安装把手(8): 用六角扳手(10)旋紧固定螺丝(9), 并塞上色扣(11), 红色朝左。



Note: Install valve 880T according to the rough-in dimensions of 8588T-4, Install valve 882T according to the rough-in dimensions of 8589T-4.

Remove the plastic guard(1) after completed the finished wall.

Slide the cover kit(4) onto the valve(3) with the plugs(13) facing outside (**Note:** Don't squeeze out the rings 12, 14). Push it against the wall. Secure it with the screws(2, length 50mm). Slide the faceplate(5) onto the valve with slots(6) downwards. Push it against the wall. Screw the bonnet(7) on the valve.

Install handle(8): Tighten the setscrew (9) with hex wrench(10). Press plug button(11) to the hole. The red part faces the left.

清理说明

适用于所有加工处理过的表面: 以中性肥皂温水清洗镀层表面, 再以干净的软布彻底擦干整个表面。许多清洁剂, 比如氨水、去污粉及洁厕灵等, 会对电镀表面造成伤害而不宜使用。

有腐蚀性的清洁剂或溶剂也不可使用时科勒牌的水龙头及其附件上。

CLEANING INSTRUCTIONS

All Finishes: Clean the finish with mild soap and warm water. Wipe entire surface completely dry with clean soft cloth. Many cleaners may contain chemicals, such as ammonia, chlorine, toilet cleaner etc. which could adversely affect the finish and are not recommended for cleaning.

Do not use abrasive cleaners or solvents on Kohler faucets and fittings.

服务零件

SERVICE PARTS

3007136
Cover Kit
安装盘组件
(仅用于8588T-4)
(Only for 8588T-4)

3007134
Cover Kit
安装盘组件
(仅用于8589T-4)
(Only for 8589T-4)

3006903
Ring
环
(仅用于8589T-4)
(Only for 8589T-4)

3006902
Ring
环

3010602
Screw
螺钉

3007064**
Faceplate
面板
(仅用于8588T-4)
(Only for 8588T-4)

3007065**
Faceplate
面板
(仅用于8589T-4)
(Only for 8589T-4)

3006992**
Bonnet
阀帽

3010604**
Handle
把手

880002
Plug Button Kit
塞扣组件

833730
2.5mm Hex Wrench
2.5毫米六角扳手

**订购时请说明颜色编号

**Color code must be specified when ordering