

### Features

- 304 stainless steel
- Self-rimming and undercounter
- Single basin
- Includes flexible trap, overflow trap, strainers, colander and installation hardware
- Exceptional sound-absorption technology (SilentShield technology)
- 480 x 416 x 204 mm

### Codes/Standards Applicable


Specified model meets or exceeds the following:

- GB/T 18884.2-2002

### Installation Notes

Install this product according to the installation guide. Allow a minimum of 2" (51 mm) clearance around the sink rim for clip attachment.

## KITCHEN SINK K-3884X



### Technical Information


Fixture:	
Basin area	434 x 370 mm
Water depth	160 mm
Drain hole	ø90 mm
*Approximate measurements for comparison only.	

Included components:	
Flexible trap	SP1200363
Strainer	SP1104787
Fixing clips	SP1071179, SP1127254
Colander	SP1097100
Template	1121206-X7

### Specified Model

Model	Description	Color/Finished
K-3884X-S	Prologue stainless steel sink	NA: None Applicable
Recommended Accessories		
K-15609X-4	Elate kitchen faucet	CP: Polished Chrome

Dimensions are approximate.  
Unit: mm



### Product Diagram

### อ่างล้างจาน K-3884X

#### คุณลักษณะ


- ผลิตจากสแตนเลส สตีล เกรด 304
- แบบฝังบนเคาน์เตอร์และฝังใต้เคาน์เตอร์
- หนึ่งหลุม
- พร้อมข้อต่อน้ำทิ้ง, ท่อน้ำล้น, สะตืออ่าง, ตะกร้าใส่ผัก และอุปกรณ์ติดตั้ง
- เทคโนโลยีโซเลนซิดด์ ช่วยลดการเกิดเสียงจากงานชาม, ลดการเกาะตัวของหยดน้ำ และช่วยรักษาอุณหภูมิของน้ำ
- 480 x 416 x 204 มม.

#### มาตรฐาน

- คุณสมบัติตามมาตรฐาน
- GB/T 18884.2-2002

#### ข้อสังเกตสำหรับการติดตั้ง

ติดตั้งผลิตภัณฑ์โดยใช้คู่มือข้อแนะนำการติดตั้ง  
เมื่อพื้นที่วางรอบขอบอ่างล้างจานไว้อย่างน้อย 2 นิ้ว (51 มม.)  
สำหรับการติดตั้งอุปกรณ์ยึดอ่างล้างจานที่มาพร้อมกับผลิตภัณฑ์



#### ข้อมูลเฉพาะ


ผลิตภัณฑ์:	
พื้นที่อ่าง	434 x 370 มม.
ระยะน้ำล้น	160 มม.
ขนาดรูท่อน้ำทิ้ง	Ø90 มม.
*ระยะค่าโดยประมาณเพื่อเปรียบเทียบเท่านั้น	

ส่วนประกอบผลิตภัณฑ์	
ข้อต่อท่อน้ำทิ้ง	SP1200363
สะตืออ่าง	SP1104787
อุปกรณ์ติดตั้ง	SP1071179, SP1127254
ตะกร้าใส่ผัก	SP1097100
กระดาดแม่แบบ	1121206-X7

#### รุ่นผลิตภัณฑ์

รุ่น	ชื่อผลิตภัณฑ์	สี/วัสดุเคลือบผิว
K-3884X-S	อ่างล้างจานสแตนเลส หนึ่งหลุม รุ่นโปรล็อก	NA: สีตามวัสดุ
<b>อุปกรณ์แนะนำ</b>		
K-15609X-4	ก๊อคมุมอ่างล้างจาน รุ่นอีเลท	CP: สีโครมเงา

ขนาดระยะแสดงค่าโดยประมาณ  
หน่วย: มม.



ภาพแสดงผลิตภัณฑ์