

### KITCHEN SINK K-3369X

#### Features

- 304 stainless steel
- Self-rimming
- Double basin
- Includes flexible trap, overflow trap, quick flow strainer, soap dispenser, colander and installation hardware
- Exceptional sound-absorption technology (SilentShield technology)
- 790 x 480 x 208 mm


#### Codes/Standards Applicable

Specified model meets or exceeds the following:

- GB/T 18884.2-2002

#### Installation Notes

Install this product according to the installation guide. Allow a minimum of 2" (51 mm) clearance around the sink rim for clip attachment.



#### Technical Information


Fixture:	Left bowl	Right bowl
Basin area	344 x 370 mm	344 x 370 mm
Water depth	198 mm	198 mm
Drain hole	ø90 mm	
Faucet hole	ø35 mm	
*Approximate measurements for comparison only.		

Included components:	
Flexible trap	SP1200369
Strainer	SP1174273, SP1141126
Fixing clips	SP1071179
Soap dispenser	2983X-NA
Colander	3368X-NA
Template	1111246-X7

#### Specified Model

Model	Description	Color/Finished
K-3369X-2KD	Staccato stainless steel sink	NA: None Applicable
Recommended Accessories		
K-12177X	Fairfax kitchen faucet	CP: Polished Chrome

Dimensions are approximate.  
Unit: mm



#### Product Diagram

#### คุณลักษณะ


- ผลิตจากสแตนเลส สตีล เกรด 304
- แบบฝังบนเคาน์เตอร์
- สองหลุม
- พร้อมข้อต่อน้ำทิ้ง, ท่อน้ำล้น, สะตืออ่างแบบควิกไฟว์, ที่ใส่น้ำยาล้างจาน, ตะกร้าใส่ผัก และอุปกรณ์ติดตั้ง
- เทคโนโลยีไฮเดนซิดด์ ช่วยลดการเกิดเสียงจากจานชาม, ลดการเกาะตัวของหยดน้ำ และช่วยรักษาอุณหภูมิของน้ำ
- 790 x 480 x 208 มม.

#### มาตรฐาน

- คุณสมบัติตามมาตรฐาน
- GB/T 18884.2-2002

#### ข้อสังเกตสำหรับการติดตั้ง

ติดตั้งผลิตภัณฑ์โดยใช้คู่มือข้อแนะนำการติดตั้ง  
เมื่อพื้นที่วางรอบขอบอ่างล้างจานไว้อย่างน้อย 2 นิ้ว (51 มม.)  
สำหรับการติดตั้งอุปกรณ์ยึดอ่างล้างจานที่มาพร้อมกับผลิตภัณฑ์



#### ข้อมูลเฉพาะ


ผลิตภัณฑ์:	หลุมซ้าย	หลุมขวา
พื้นที่อ่าง	344 x 370 มม.	344 x 370 มม.
ระยะน้ำล้น	198 มม.	198 มม.
ขนาดรูท่อน้ำทิ้ง	Ø90 มม.	
ขนาดรูท่อน้ำ	Ø35 มม.	
*ระยะค่าโดยประมาณเพื่อเปรียบเทียบเท่านั้น		

ส่วนประกอบผลิตภัณฑ์	
ข้อต่อท่อน้ำทิ้ง	SP1200369
สะตืออ่าง	SP1174273, SP1141126
อุปกรณ์ติดตั้ง	SP1071179
ที่ใส่น้ำยาล้างจาน	2983X-NA
ตะกร้าใส่ผัก	3368X-NA
กระดาดแม่แบบ	1111246-X7

#### รุ่นผลิตภัณฑ์

รุ่น	ชื่อผลิตภัณฑ์	สี/วัสดุเคลือบผิว
K-3369X-2KD	อ่างล้างจานสแตนเลส สองหลุม รุ่นสตักคาโต้	NA: สีตามวัสดุ
อุปกรณ์แนะนำ		
K-12177X	ก๊อกลงอ่างล้างจาน รุ่นแฟร์แพกซ์	CP: สีโครมเงา

ขนาดระยะแสดงค่าโดยประมาณ  
หน่วย: มม.



ภาพแสดงผลิตภัณฑ์