


Features

- *Acrylic and reinforced with fiberglass*
- *Drop-in*
- *Includes pillow head*
- *Includes pop-up drain and overflow*
- *Coordinates with Patio suite*
- *1700 x 800 x 450 mm*

BATH

K-18257X



Codes/Standards Applicable

Specified model meets or exceeds the following:

- *ANSI Z124.1.2*
- *TIS 2141-2546*

Colors/Finishes

- 0: White

Accessories:

- CP: Polished Chrome

Specified Model

Model	Description	Color/Finished
K-18257X	Patio 1700 plain bath	0

Product Specification:

The Patio bath shall be 1700 mm in length, 800 mm in width, and 450 mm in height. Bath shall be made of acrylic and reinforced with fiberglass. Bath shall be drop-in installation. Bath shall be coordinating Patio suite. Bath shall include pillow head, pop-up drain and overflow. Bath shall be Kohler Model K-18257X-_____.

PATIO 1700

Technical Information


Fixture*:	
Basin area:	
Basin area bottom	1062 x 488 mm
Basin area top	1579 x 741 mm
To overflow:	
Water depth	303 mm
Capacity	240 liters
Drain hole	ø38 mm (1-1/2")
Overflow hole	ø52 mm
Weight	22 kg
*Approximate measurements for comparison only.	

Installation Notes

Install this product according to the installation guide.

Floor support under bath must provide for a minimum of 339 kg/square meter loading.

Dimensions are approximate.
Unit: mm




Product Diagram

คุณลักษณะ

- อะคริลิคเสริมใยแก้ว
- แบบฝัง
- พร้อมหมอนรองศีรษะ
- พร้อมสะดืออ่างแบบป๊อปอัพและท่อน้ำล้น
- เหมาะสำหรับสุขภัณฑ์ชุดแพททีโอ
- 1700 x 800 x 450 มม.

อ่างอาบน้ำ

K-18257X



มาตรฐาน

คุณสมบัติตามมาตรฐาน

- ANSI Z124.1.2
- มอก. 2141-2546

สี/วัสดุเคลือบผิว

- 0: สีขาว

ส่วนประกอบอื่นๆ:

- CP: สีโครมเงา

รุ่นผลิตภัณฑ์

รุ่น	ชื่อผลิตภัณฑ์	สี/วัสดุเคลือบผิว
K-18257X	อ่างอาบน้ำ รุ่น แพททีโอ 1700	0

ข้อมูลผลิตภัณฑ์:

อ่างอาบน้ำแพททีโอมีขนาดยาว 1700 มม. กว้าง 800 มม. และสูง 450 มม. ซึ่งผลิตจากวัสดุอะคริลิคเสริมใยแก้ว อ่างอาบน้ำติดตั้งแบบฝัง อ่างอาบน้ำเหมาะกับสุขภัณฑ์ชุดแพททีโอ อ่างอาบน้ำพร้อมหมอนรองศีรษะ, สะดืออ่างแบบป๊อปอัพและท่อน้ำล้น อ่างอาบน้ำรุ่นนี้คือ อ่างอาบน้ำโคห์เลอร์รุ่น K-18257X-_____.

แพททีโอ 1700

ข้อมูลเฉพาะ


สุขภัณฑ์:	
พื้นที่อ่างอาบน้ำ:	
พื้นที่ด้านล่าง	1062 x 488 มม.
พื้นที่ด้านบน	1579 x 741 มม.
ระดับน้ำ:	
ระดับน้ำลึก	303 มม.
ความจุน้ำ	240 ลิตร
รูท่อน้ำทิ้ง	Ø38 มม. (1-1/2")
รูท่อน้ำล้น	Ø52 มม.
น้ำหนัก	22 กิโลกรัม
*ระยะค่าโดยประมาณเพื่อการเปรียบเทียบเท่านั้น	

ข้อสังเกตสำหรับการติดตั้ง

ติดตั้งสุขภัณฑ์โดยใช้คู่มือข้อแนะนำการติดตั้ง

พื้นที่ใช้รองรับอ่างอาบน้ำต้องสามารถรับน้ำหนักอย่างน้อย 339 กก./ตร.ม.

ขนาดระยะแสดงค่าโดยประมาณ
หน่วย: มม.



ภาพแสดงผลิตภัณฑ์

อ่างอาบน้ำ รุ่น แพททีโอ 1700
หน้า 4/4
1072714-X4-B

KOHLER®