

### Features

- Brass valve bodies
- Quarter-turn washerless ceramic disc valves
- Includes pop-up drain with lift rod and tailpiece
- 4" (102 mm) center of spout
- 100 mm spout reach
- Lever handle

### 4" CENTEREST LAVATORY FAUCET K-7502X-4



### Codes/Standards Applicable

Specified model meets or exceeds the following:

- TIS 2067-2552

### Colors/Finishes

- CP: Polished Chrome

### Accessories:

- CP: Polished Chrome

### Specified Model

Model	Description	Color/Finished
K-7502X-4	Archer 4" centerest lavatory faucet	CP

### Product Specification:


The two-handle centerest lavatory faucet shall be made of brass valve bodies. Product shall feature quarter-turn washerless ceramic disc valves. Product shall feature 100 mm spout reach. Product shall be 4" (102 mm) centers. Product shall include lever handle. Product shall have a pop-up drain with lift rod and tailpiece. Faucet shall be Kohler Model K-7502X-4-CP.

# ARCHER

## Installation Notes

Install this product according to the installation guide.

Dimensions are approximate.  
Unit: mm.



## Product Diagram

### คุณลักษณะ

- ตัววาล์วทองเหลือง
- เซรามิกวาล์ว แบบหมุน 90 องศา
- พร้อมสະดืออ่างแบบป็อบอัฟ
- เซ็นเตอร์ 4" (102 มม.)
- ระยะจากกึ่งกลางตัวก๊อกถึงกึ่งกลางปากก๊อก 100 มม.
- มือบิดแบบก้านโยก

### ก๊อกผสมอ่างล้างหน้า เซ็นเตอร์ 4" K-7502X-4



### มาตรฐาน

คุณสมบัติตามมาตรฐาน

- มอก. 2067-2552

### สี/วัสดุเคลือบผิว

- CP: สีโครมเงา

### ส่วนประกอบอื่นๆ:

- CP: สีโครมเงา

### รุ่นผลิตภัณฑ์

รุ่น	ชื่อผลิตภัณฑ์	สี/วัสดุเคลือบผิว
K-7502X-4	ก๊อกผสมอ่างล้างหน้า เซ็นเตอร์ 4" รุ่น อาร์เซอร์	CP

### ข้อมูลผลิตภัณฑ์:


ก๊อกผสมอ่างล้างหน้าแบบ 2 มือบิด ผลิตจากวาล์วทองเหลือง วาล์วก๊อกน้ำเป็นเซรามิกวาล์วแบบหมุน 90 องศา ก๊อกน้ำมีระยะกึ่งกลางจากตัวก๊อกถึงกึ่งกลางปากก๊อก 100 มม. ก๊อกน้ำติดตั้งแบบเซ็นเตอร์ 4" (102 มม.) ก๊อกน้ำพร้อมมือบิดแบบก้านโยก ก๊อกน้ำพร้อมสະดืออ่างแบบป็อบอัฟ ก๊อกน้ำรุ่นนี้คือก๊อกน้ำโคห์เลอร์รุ่น K-7502X-4-CP

# อาร์เซอร์

## ข้อสังเกตสำหรับการติดตั้ง

ติดตั้งผลิตภัณฑ์โดยใช้คู่มือข้อแนะนำการติดตั้ง

ขนาดระยะแสดงค่าโดยประมาณ  
หน่วย: มม.



## ภาพแสดงผลิตภัณฑ์

ก๊อกผสมอ่างล้างหน้า เซ็นเตอร์ 4" รุ่น อาร์เซอร์

หน้า 4/4

1153000-X4-A

**KOHLER**®