

### Features

- Brass construction
- Single-hole mounting
- One-piece, self-contained ceramic disc valve allows both volume and temperature control
- Flexible connection for easy installation
- Includes pop-up drain with lift rod and tailpiece
- 103 mm spout reach
- Lever handle

### SINGLE-HOLE SINGLE CONTROL LAVATORY FAUCET K-37327X-4



### Codes/Standards Applicable

Specified model meets or exceeds the following:

- TIS 2067-2552

### Colors/Finishes

- CP: Polished Chrome

### Accessories:

- CP: Polished Chrome

### Specified Model

Model	Description	Color/Finished
K-37327X-4	Strayt single-hole single control lavatory faucet	CP

### Product Specification:


The single-hole single-control lavatory faucet shall be made of brass construction. Product shall feature a one-piece, self-contained ceramic disc valve, allowing volume and temperature control. Product shall be for single-hole mounting. Product shall feature a 103 mm spout reach, lever handle, pop-up drain with lift rod and tailpiece, flexible connections for easy installation. Faucet shall be Kohler Model K-37327X-4-CP.

# STRAYT

## Installation Notes

Install this product according to the installation guide.

Dimensions are approximate.  
Unit: mm.



## Product Diagram

### คุณลักษณะ

- ผลิตจากทองเหลือง
- ติดตั้งแบบรูก๊อกเดี่ยว
- เซรามิควาล์ว วาล์วกักน้ำเดี่ยวควบคุมทั้งปริมาณน้ำและอุณหภูมิ
- ติดตั้งด้วยสายน้ำดี ทำให้ติดตั้งง่าย
- พร้อมสະดืออ่างแบบป๊อปอัพ
- ระยะกึ่งกลางจากตัวก๊อกถึงกึ่งกลางปากก๊อก 103 มม
- มือบิดแบบก้านโยก

### ก๊อกผสมอ่างล้างหน้าแบบก้านโยก K-37327X-4



### มาตรฐาน

คุณสมบัติตามมาตรฐาน

- มอก. 2067-2552

### สี/วัสดุเคลือบผิว

- CP: สีโครมเงา

### ส่วนประกอบอื่นๆ:

- CP: สีโครมเงา

### รุ่นผลิตภัณฑ์

รุ่น	ชื่อผลิตภัณฑ์	สี/วัสดุเคลือบผิว
K-37327X-4	ก๊อกผสมอ่างล้างหน้าแบบก้านโยก รุ่น สเตย์ท	CP

### ข้อมูลผลิตภัณฑ์:


ก๊อกผสมอ่างล้างหน้าผลิตจากทองเหลือง วาล์วกักน้ำเป็นเซรามิควาล์ว กักน้ำวาล์วเดี่ยวที่ควบคุมทั้งปริมาณน้ำและอุณหภูมิ ก๊อกน้ำแบบรูก๊อกเดี่ยว มีระยะจากกึ่งกลางตัวก๊อกถึงกึ่งกลางปากก๊อก 103 มม. ก๊อกน้ำแบบก้านโยกพร้อมสະดืออ่างแบบป๊อปอัพ ติดตั้งด้วยสายน้ำดีทำให้ติดตั้งได้ง่าย ก๊อกน้ำรุ่นนี้คือ ก๊อกน้ำโคห์เลอร์รุ่น K-37327X-4-CP

# สเตย์ท

## ข้อสังเกตสำหรับการติดตั้ง

ติดตั้งผลิตภัณฑ์โดยใช้คู่มือข้อแนะนำการติดตั้ง

ขนาดระยะแสดงค่าโดยประมาณ  
หน่วย: มม.



## ภาพแสดงผลิตภัณฑ์