



STRONG. PROFESSIONAL. DESIGN.™

# S P E C I F I C A T I O N S

## Bath Classics™ Vista-Glide II™ Tri-Panel Tub Doors

Models 1701D, 1720D, 1762D

### Standard Features


- Wide opening for easy access.
- Anodized aluminum-framed sliding glass doors
- Durable nylon-faced ball-bearing adjustable rollers
- Full length center mirror
- Easy-to-clean track with Grip-Lock™ panel guide system
- Low profile decorative handles
- Tempered glass ensures maximum safety
- Frame components extruded from aluminum alloy 6063-T5
- All necessary hardware included

### Standards and Ratings

- Tempered glass complies with ANSI Z97.1-1984 and Architectural Glazing Standard 16CFR1201





### Optional Features

- Bright silver, polished brass, or bright gold frame finishes
- Pebbled texture, tinted horizontal or radiant striped, symmetry, or beveled glass panels
- Available in 56" or 60" models



Unique bottom track guides doors.

Low-profile handles add safety, convenience, and style.



### Features

#### Tempered glass

#### Grip-Lock™ guide system

#### Easy-to-clean track

#### Versatile designs

#### Optional towel bar

#### Hide-away towel/robe hook

#### Stainless steel hardware

### Benefits

Tempered glass offers maximum safety and durability.

Grip-Lock™ panel guide system locks the full width of the panel into the bottom track. Doors slide effortlessly, quietly.

Bottom track directs water back into tub and minimizes soap or lint build up.

Optional frame finish and panel pattern offer maximum versatility.

Choose from a convenient towel bar or low profile handle attachment.


Convenient hook swings in for wet items; swings out for towel or robe.

Prevents fasteners from rusting or corroding in a damp environment.

**Bath Classics™**  
**Vista-Glide II™**  
**Tri-Panel Tub Doors**

Models 1701D, 1720D, 1762D

D I M E N S I O N S



Model	Frame Finish	Glass Panel Pattern	Door Height	Max. Opening
1701D-56S	Silver	Brown Tint/ Beige Stripes	57 $\frac{1}{8}$ "	56"
1701D-56G	Polished Brass	Brown Tint/ Beige Stripes	57 $\frac{1}{8}$ "	56"
1700D-60S	Silver	Pebbled Texture	57 $\frac{1}{8}$ "	60"
1701D-60S	Silver	Brown Tint/ Beige Stripes	57 $\frac{1}{8}$ "	60"
1701D-60G	Polished Brass	Brown Tint/ Beige Stripes	57 $\frac{1}{8}$ "	60"
1710D-60S	Silver	Pebbled Texture/ No Mirror	57 $\frac{1}{8}$ "	60"
1720D-60S	Silver	Clear/V-Beveled	57 $\frac{1}{8}$ "	60"
1720D-60G	Polished Brass	Clear/V-Beveled	57 $\frac{1}{8}$ "	60"
1762D-60S	Silver	Clear/White Stripes	57 $\frac{1}{8}$ "	60"
1762D-60PB	Polished Brass	Clear/White Stripes	57 $\frac{1}{8}$ "	60"

