

















KALLISTA®

Installation Guide




<p>⚠ WARNING: Risk of scalding. High water temperature can cause severe burns. Set the water temperature at or below 120°F (49°C) following the adjustment procedure in this document.</p>	<p>⚠ WARNING: Risk of scalding. This valve will not protect against scalding if incoming water temperature changes significantly during operation.</p>	<p>⚠ CAUTION: Risk of product damage: Use only silicone based lubricants with this product. Other lubricants may cause damage.</p>	<p>Observe all local plumbing and building codes. Record your model number below for future reference:</p>	<p>This valve meets or exceeds ANSI A112.18.1/CSA B125.1/ASSE 1016.</p>
<p>1 Turn off the water supply to the valve. If the test cap is installed, remove it now.</p> 	<p>2 Confirm the O-rings are undamaged and properly seated around each port and the base.</p> 	<p>3 Align the "COLD" mark with the cold water supply.</p> 	<p>4 Confirm the aspirator is aligned with the showerhead outlet. Reverse the aspirator if needed.</p> 	<p>To reverse the aspirator, push it out with a screwdriver and reinstall in the opposite port.</p> 
<p>5 Install the cartridge with the "COLD" port aligned with the cold supply.</p> 	<p>6 Turn on the water supply. Turn the valve stem clockwise to the full hot position.</p> 	<p>⚠ WARNING: Risk of scalding. Do not set the water temperature above 120°F (49°C).</p>	<p>7 Measure the maximum water temperature. If the water is too hot or cold, adjustment is required.</p> 	<p>8 Temperature Adjustment: Remove the plaster guard or trim (not shown) if installed. Remove the warning tag and stop.</p> 
<p>Turn on the water. Adjust the valve stem until the desired maximum temperature is found.</p> 	<p>With the water still on, reinstall the stop against the tab.</p> 	<p>If finer adjustment is needed, reverse the stop.</p> 	<p>Turn off the valve using the plaster guard.</p> 	<p>Reinstall the warning tag. If the finished wall is not installed reinstall the plaster guard (not shown).</p> 

9 Install a deep rough-in kit if "A" is less than 1-1/4" (32 mm).

10 IMPORTANT! To determine the correct deep rough-in kit, go to the www.kallista.com page for this product and refer to the specification sheet.

11 Install the shower trim following the instructions provided with the trim.



FIVE-YEAR LIMITED WARRANTY

All Kallista products carry Kallista's five-year limited warranty unless otherwise noted.*

Kallista products are warranted to be free of defects in material and workmanship for five years from the date of installation.

Kallista will, at its election, repair, replace or make appropriate adjustment where Kallista inspection discloses any such defects occurring in normal usage within five (5) years after installation.

Kallista is not responsible for removal or installation costs.

Damages due to improper handling, installation or maintenance are not considered manufacturing defects and are not covered by this warranty. This warranty is valid for the original consumer purchaser only.

To obtain warranty service, contact your Kallista Authorized Showroom.

Products must be maintained and cleaned in accordance with the care and cleaning instructions provided by Kallista. Improper care or cleaning, including damage from the use of abrasive chemicals, will void this warranty. Gloss reduction, scratching, staining and alkaline etching of finishes over time due to use, cleaning practices or water or atmospheric conditions, are not manufacturing defects but are indicative of normal wear and tear. Use of in-tank toilet cleaners will void the warranty.

Implied warranties including that of merchantability and fitness for a particular purpose are expressly limited in duration to the duration of this warranty. Kallista and/or seller disclaims any liability for special, incidental, or consequential damages.

Some states/provinces do not allow limitations on how long an implied warranty lasts, or the exclusion or limitation of special, incidental or consequential damages, so these limitations and exclusions may not apply to you. This warranty gives you specific legal rights. You may also have other rights which vary from state/province to state/province.

This is Kallista's exclusive written warranty.

* Kallista's Hampstead and Stafford vitreous products, stainless steel accessories, and wooden accessories carry a one-year Limited Warranty.

Questions? Problems? For additional assistance, please contact KALLISTA's Customer Service Department at 1-888-4-KALLISTA (1-888-452-5547) or kallista.com.