

Features

- Slim Museum Frame: for a shadow box effect and to complement a modern aesthetic, the sleek profile creates a minimalist look
- Features a 3/8" gap between the edge of the mirror and the overall frame to create an even, uniformed illumination
- Match fixtures with metal frame finishes: Chrome, Polished Nickel, Matte Gold, Matte Black
- Includes mirror defogging
- Dimmable LED task lighting to 1%
- Front and side diffuser, no visible LEDs
- Energy efficient LED lighting

Lighting Specs

Kelvin:	3000K
CRI:	90+
Lumenst:	1270-1560
R9 Value:	50+
Lux†:	400-490
Foot-candles†:	37-45

†Measured at 18" from center of mirror

Construction

- Plated chrome and polished nickel finishes provide easy upkeep, exceptional durability, and a timeless look that complements any design
- Anodized matte gold and matte black finish options are easy to maintain and won't chip, peel, or fade – so you can enjoy their beauty for years to come
- Anodized aluminum back frame
- Quality polished edge mirror
- Power cords installed for easy plugin installation
- Constructed for surface mounting
- Includes installation hardware


Dimensions

- 25-1/4" x 31-1/4" x 2-1/4" (641 mm x 794 mm x 57 mm)
- 25-1/4" x 41-1/4" x 2-1/4" (641 mm x 1048 mm x 57 mm)

Codes/Standards Applicable

Framed Lighted Mirror is UL certified to:

- UL 962
- CSA-C22.2, No. 250.4




Savant Model Number	Product Description
SVTFM02430NC3PSO	Framed Lighted Mirrors, 25" x 31", Slim Museum Frame, Chrome, 3000K
SVTFM02430NN3PSO	Framed Lighted Mirrors, 25" x 31", Slim Museum Frame, Polished Nickel, 3000K
SVTFM02430NG3PSO	Framed Lighted Mirrors, 25" x 31", Slim Museum Frame, Matte Gold, 3000K
SVTFM02430NB3PSO	Framed Lighted Mirrors, 25" x 31", Slim Museum Frame, Matte Black, 3000K

Savant Model Number	Product Description
SVTFM02440NC3PSO	Framed Lighted Mirrors, 25" x 41", Slim Museum Frame, Chrome, 3000K
SVTFM02440NN3PSO	Framed Lighted Mirrors, 25" x 41", Slim Museum Frame, Polished Nickel, 3000K
SVTFM02440NG3PSO	Framed Lighted Mirrors, 25" x 41", Slim Museum Frame, Matte Gold, 3000K
SVTFM02440NB3PSO	Framed Lighted Mirrors, 25" x 41", Slim Museum Frame, Matte Black, 3000K

Electrical System

- 120 VAC 60HZ wall outlet as shown in drawing



*For 24x40 size mirror

See instructions 209-1308 for wiring and location