

THIS PAGE DEPICTS MODELS:
K-1476-H-AA, K-1476-H-AB
K-1476-V-AA, K-1476-V-AB

INFINITY[∞]BATH™ WHIRLPOOLS

SERVICE PARTS

ITEM NO.	REV. AA	REV. AB	REV. AC	DESCRIPTION
1	67429	67429		Jet Flange
2	K-9696	K-9696	‡	Trim Kit
3	105813	105813	§	Suction Assembly
4	106474	106474	§	Whirlpool Control Assembly
5	65156	65156	‡	Switch Flange
6	31456	31456	‡	Retainer Cap
7	K-9587	K-9587	‡	Trim Kit
	K-9589	K-9589	‡	Trim Kit
	K-9599	K-9599	‡	Trim Kit
8	31001	31001		Supply Valve
9	31448	31448		Clamp
10	31446	31446		Tube
11	62457	62457		Drain Closer Master Assembly
12	21147	21147		Overflow Washer
13	35278	35278		Washer
14	35277	35277		Gasket
15	62464	62464		Retainer
16	31455	31455		Retainer Body
17	32010	32010		Nut
18	60745	60745		Diverter Seal
19	21149	21149		Retainer Plate
20	21148	21148		Screw
21	35279	35279	‡	Fill Spout
22	65157	65157		Finger Nut
23	K-9590	K-9590	‡	Autofill Mixer Trim Kit
	K-9591	K-9591	‡	Autofill Mixer Trim Kit
	K-9603	K-9603	‡	Autofill Mixer Trim Kit
24	24003	24003		Nut, 1-1/4"-14
25	24899	24899		Union Joint
26	65109	65109		1/2" Nom. Copper Tube
27	60024	60024		Tee
28	62484	62484		Level Sensor Assembly
29	65093	65093		Water Control Master
30	65108	65108		1/2" Nom. Copper Tube
31	62509	62509		Compression Fitting
32	60206	60206		Elbow
33	65107	65107		1/2" Nom. Copper Tube
34	65113	65113		1/2" Nom. Copper Tube
35	62473	62473		Adapter
36	65124	65124		Adapter
37	62431	62431		Strainer
38	91017	91017		Check Valve Service Kit
39	61563	61563		Tee
40	65273	65273		1" Nom. PVC Tube
41	67665	67665		Plug
42	67889	67889		Jet Housing
43	68370	68370		1" Nom. PVC Tube
44	66590	66590		1" Nom. PVC Tube
45	66589	66589		1" Nom. PVC Tube
46	68526	91745		1" Nom. PVC Tube
47	61536	61536		Elbow
48	N/A	60125		Washer, 1/4" Lock
49	64163	64163		Screw, 1/4"-20
50	N/A	65791		Washer, 5/16" Int./Ext.
51	N/A	90987		Pump Bracket
52	N/A	67111		Washer, 3/8"
53	N/A	91150		Bolt, 5/16"
54	90155	N/A		Locknut, 3/8"-16
55	90154	90154		Locknut, 5/16"-18
56	65791	N/A		Washer, 5/16" Int./Ext.
57	67417	N/A		Motor Support Bracket
58	67095	67095		Washer, 5/16" Flat
59	60910	60910	■	Motor and Pump
60	67109	N/A		Bolt, 5/16"-18
61	68577	68577		Cord Grip
62	60797	60797		Tee
63	N/A	91745		1" Nom. Flex Tube
64	60979	60979		Slip Nut

SERVICE PARTS

ITEM NO.	REV. AA	REV. AB	REV. AC	DESCRIPTION
65	60848	60848		Connector
66	60980	60980		O-Ring
67	60714	60714		Elbow
68	68369	91741		1-1/4" Nom. PVC Tube
69	N/A	66265		Coupling
70	N/A	91744		1-1/4" Nom. Flex Tube
71	106473	106473	§	Suction Assembly
72	*	*		Airline Tube
73	66585	N/A		1" Nom. PVC Tube
74	N/A	60561		Reducer
75	66588	91448		PVC Tube
76	65885	65885		Gasket
77	69849	69849		1" Nom. PVC Tube

OPTIONAL HEATER SERVICE PARTS



ITEM NO.	REV. AA	REV. AB	REV. AC	DESCRIPTION
78	60845	60845		Connector
79	65301	65301		1-1/2" Nom. PVC Tube
80	64212	N/A		Washer, 1/4" Flat
81	106475	106475	§	Whirlpool Heater Assembly
82	65331	65331		Band Seal
83	68368	91741		1-1/4" Nom. PVC Tube
84	65558	N/A		Heater Support Bracket
85	90153	90153		Locknut, 1/4"-20
86	65574	N/A		Heater Support Bracket
87	N/A	90608		Heater Support Strap

NOTES & LEGEND

- Parts Further Exploded Within This Catalog.
- ‡ Specify Color/Finish
- § Reference Number Only
- * For 120" of Plastic Tube, Order 61972
- N/A Not Applicable For This Model

KOHLER® SERVICE PARTS

WHIRLPOOL TRIM KITS
4 Jet Kit K-9694, 5 Jet Kit K-9695
6 Jet Kit K-9696, 8 Jet Kit K-9698




Service Parts

Item No.	Part No.	Qty.	Description	Specifications
1	65042	†	4-5 Directional Jet (Plated Metal)	
1	65044	†	4-5 Directional Jet (Colored Plastic)	
1	65205	†	6-8 Directional Jet (Colored Plastic With Orifice)	
1	65206	†	6-8 Directional Jet (Plated Metal With Orifice)	
2	67594		O-Ring	
3	65226	†	Cover Button (Colored Plastic)	
4	65054	†	Screw	
5	30777	†	Suction Cover (Colored Plastic)	
5	30778	†	Suction Cover (Plated Metal)	
6		†	Retainer Plate (Included With #30777)	
7	30739	1	Directional Jet Removal Tool	
8	30746	1	Jet Flange Removal Tool	

Service Kits

NOTES:

† Specify Finish.
Items 3-6 not packed with colored plastic trim kits.
Item 6 not packed with plated metal trim kits.



SERVICE PARTS

ITEM NO.	PART NO.	DESCRIPTION
1	65226‡	Plug, (Used on Plastic Suction Cover Only)
2	65054‡	Screw, #10-24
3	65061‡	Suction Cover, Brass
	67999‡	Suction Cover, Plastic
4		Available in Service Kit Only
5		Available in Service Kit Only

SERVICE KITS

PART NO.	ITEM NO.	QTY.	DESCRIPTION
92141‡			Suction Hood Kit, Brass
	2	1 ea.	Screw, #10-24
	3	1 ea.	Suction Cover, Brass
92142‡			Suction Hood Kit, Plastic
	1	1 ea.	Plug
	2	1 ea.	Screw, #10-24
	3	1 ea.	Suction Cover, Plastic
	4	1 ea.	Retainer Plate

NOTES & LEGEND


- ‡ Specify Color/Finish
- § Reference Number Only

KOHLER® SERVICE PARTS

WHIRLPOOL POWER PANEL and CONTROL

106474§

SERVICE SERIES CODE - PS



Service Parts

Item No.	Part No.	Qty.	Description	Specifications
1	500407	†	Strain Relief Kit	
2	30790	†	Circuit Board	
3	30789	†	Cover (Includes 4 Screws)	
4	30788	†	Attachment Kit	
5	91239	†	Air Switch	
6	30775	†	Whirlpool Control (Includes 9)	
7	30774	†	Whirlpool Control (With Heater, Includes 8)	
8	500405	†	Decal (With Heat)	
9	500406	†	Decal (Whirlpool Only)	

Service Kits:

Items:

† 1-5, #500460■ Power Panel Kit.

NOTES:

* For 120" of Plastic Tube, Order #61972.


** Includes 72" Cable.

■ Parts Further Exploded Within This Catalog. Reference Index.

§ Reference Number Only.

KOHLER® SERVICE PARTS

AUTOFILL™ MIXER TRIM KIT
K-9590 BRAVURA™, K-9591 FLAIR II™
K-9603 ALTERNA™



Service Parts


Item No.	Part No.	Qty.	Description	Specifications
1	62490	1	Button	
2	43146	1	Handle	
3	41240†	1	Insert	
4	43167†	1	O-Ring	
5	43273	1	Stem Extension	
6	20652†	1	Screw	
7	41298†	1	Washer	
8	62488†	1	Cap	
9	31435†	1	Handle	
10	48694	1	O-Ring	
11	33357†	1	Screw (CP)	
12	62489†	1	Escutcheon	
13	22491†	1	Shell	
14	22493-O	2	Inset (white)	
14	22493-7	2	Inset (black)	
14	22494-G	2	Inset (gold finish)	
15	22454	1	Retaining Cap	
16	63894	1	Screw	
17	22490	1	Adapter	
18	46034	1	Lock Ring	
19	22457†	1	Skirt Handle	

Service Kits

Items:
† 4, 6, 7, #30047, Flair Handle Rebuilding Kit

NOTES:

† Specify Finish.




SERVICE PARTS

ITEM	PART NO.	DESCRIPTION
1	60982	Screw, 10-32 UNF, Sit Hex, Wash.Hd.
2	60926	Cover
3	60981	O-Ring
4	60993	Impeller, 3/4 HP
	60994	Impeller, 1 HP
5		Available in Service Kit Only
6	60985	Shaft Seal
7	60927	Volute Assembly
8	60972	Slinger
9		Not Available As A Service Part
10	74823	End Cap
11	62726	Screw
12	74824	Machine Bolt

SERVICE KITS

PART NO.	ITEM	QTY.	DESCRIPTION
67631			Seal Kit
	3	1 ea.	O-Ring
	6	1 ea.	Shaft Seal
	8	1 ea.	Slinger
60912			Shim Kit
	5	2 ea.	Shim, .010



SERVICE PARTS

ITEM NO.	PART NO.	DESCRIPTION
1	65055	Suction Housing
	65056	Suction Housing, (Illustrated)
2	60050	Tapered Gasket, (For Cast Iron Whirlpools)
	65886	Tapered Gasket, (For Acrylic Whirlpools)
3	65036**	Suction Flange
4	65059	Tube, Suction Housing
5	65122	Elbow, Rubber




SERVICE KITS

PART NO.	ITEM NO.	QTY.	DESCRIPTION
30670	1-5	1	Suction Replacement Kit, (Includes 65055 and Flexible PVC)
30748	1-5	1	Suction Replacement Kit, (Includes 65056 and Flexible PVC)



NOTES & LEGEND

- § Reference Number Only
- * For 120" of Plastic Tube, Order 61972
- ** For Suction Flange Removal Tool, Order 30706

ORIENTATION DETAILS



ORIENTATION DETAILS



SERVICE PARTS

ITEM NO.	PART NO.	DESCRIPTION
1	65194	Heater Flange Assembly
2	68686	Cord
3	Available in Service Kit Only	
4	30789	Cover
5	Available in Service Kit Only	
6	65186	Knob, Thermostat
7	69079	Screw
8	60320	Screw
9	64463	Washer
10	64460	Washer
11	67264	Strain Relief Bushing
12	63563	Screw
13	Available in Service Kit Only	
14	69473	Nut
15	60125	Washer, Lock
16	69472	Washer
17	65197	O-ring

SERVICE KITS

PART NO.	ITEM NO.	QTY.	DESCRIPTION
65182	1-12	1	Whirlpool Heater Assembly, (Illustrated)
65183	1-12	1	Whirlpool Heater Assembly
65533	1-12	1	Whirlpool Heater Assembly
65741	1-12	1	Whirlpool Heater Assembly
500346	3,10,12	1	High Limit Switch Kit
500345	5-7,9	1	Thermostat Kit
500386	13-16	1	Heater Casting Kit

NOTES & LEGEND

§ Reference Number Only