
KOHLER® SERVICE PARTS

ELATE

13963T-B4 Pull Out Kitchen Faucet



KOHLER[®] INSTALLATION INSTRUCTIONS

13963T-B4 Pull Out Kitchen Faucet

BEFORE YOU BEGIN

All information is based on the latest product information available at the time of publication. Kohler Co. reserves the right to make changes in product characteristics, packaging, or availability at any time without notice.

Please leave these instructions for the consumer. They contain important information.

NOTES:

1. Flush the water supply pipes thoroughly to remove debris.

2. For new installations, assemble the faucet to sink before installing.

3. The highest working pressure for handspray & shower head is 0.5MPa(5bar). If it exceeds 0.5MPa(5bar), a pressure reducer is needed. The highest water and environment temperature is 60°C. Please keep handspray, shower head and the shower arm away from heater, or it may become damaged and cause injury to the user.


HANDLE OPERATION

Lift the handle gently. Turn clockwise for cold water, turn counter-clockwise for hot water.

ROUGH-IN DIMENSIONS

82 82 1700

ELATE



INSTALLATION

How To Install The Faucet

If the escutcheon kit(1) isn't slided into the groove on the bottom of the body(2), then you need to slide it into the groove on the bottom of the body. Insert the hoses and mounting studs(3) into the mounting hole of the sink. Let the bottom of the body against the deck.

From underside of the sink, fit the mounting bracket(4) on the mounting studs. Position the faucet so that the spray hose(5) is on the left, the spray hose and two hoses(6) are symmetrical. Tighten two nuts(8) with wrench(7) to the mounting studs so that they can secure faucet to sink.

Attach the hoses to water supplies. When facing the faucet, the hose in front connects to hot water, the back hose with 'COLD' label connects to cold water.


Put the weight(10) and clip(11) onto the hose(5). Adjust the weight so that the distance is right from the bottom of the faucet to the weight. Insert the hose(5) into the connector(9).

How To Use Spray

Open the handle, if you want to use the spray by hand, take the spray and pull out the hose.

Press the button(A) as shown for the water close. Press the button(B), (C) as shown for two different forms of water flow, as figure(a), (b) shown.

NOTE: Please pull it gently and do not draw out the spray hose too long, or you may damage the hose and connector.



INSTALLATION CHECKOUT

Ensure that all coupling nuts are tight. Ensure that the lever handle is in the off position. Turn on the main water supply and drain, and check for leaks. Repair as needed.

Remove the spray(12). Run hot and cold water about one minute to remove any debris. Remove any debris from the filter washer and aerator of the spray. Shut off the faucet. Reinstall the spray.

CLEANING INSTRUCTIONS

All Finishes: Clean the finish with mild soap and warm water. Wipe entire surface completely dry with clean soft cloth. Many cleaners may contain chemicals, such as ammonia, chlorine, toilet cleaner etc, which could adversely affect the finish and are not recommended for cleaning.

Do not use abrasive cleaners or solvents on Kohler faucets and fittings.

"LEAD FREE" is marked on the back of the faucet signifying its compliance with the United States AB1953

