

KITCHEN SINK K-3882X

Features

- 304 stainless steel (Fabricated stainless steel)
- Undercounter
- Double (large/medium) compartment
- Includes S-trap, overflow trap, quick flow strainer installation hardware, cutting board and wire basket
- Exceptional sound-absorption technology (SilentShield technology)
- 820 x 430 x 228 mm


Codes/Standards Applicable

Specified model meets or exceeds the following:

- ANSI A112.19.3M/CSA B45.4
- QB/T 4013

Installation Notes

Install this product according to the installation guide.



Technical Information

Fixture:	Left	Right
Basin area	335 x 460 mm	270 x 335 mm
Water depth	150 mm	180 mm
Drain hole	38 or 51 mm (1-1/2" or 2")	
*Approximate measurements for comparison only.		

Included components:	
S-trap	1200369
Strainer	5163T-NA/1174273
Fixing clips	1127254
Cutting board	1108778
Wire basket	1108799
Template	1110885-X7


Specified Model

Model	Description	Color/Finished
K-3882X-F	Poise kitchen sink	NA: None Applicable

Recommended Accessories		
K-18006X	Nateo kitchen faucet	CP: Polished Chrome

Dimensions are approximate.

Unit: mm



Product Diagram

อ่างล้างจาน K-3882X

คุณลักษณะ


- ผลิตจากสแตนเลส สเต็ล เกรด 304 (Fabricated stainless steel)
- แบบฝังใต้เคาน์เตอร์
- สองหลุม (ขนาดใหญ่/ขนาดกลาง)
- พร้อมข้อต่อน้ำทิ้งแบบลงพื้น, ท่อน้ำล้นในตัว, สะดืออ่างแบบควิกไฟว์, อุปกรณ์ติดตั้ง, เชียง และตะกร้า
- เทคโนโลยีไฮเดรนซิลด์ ช่วยลดการเกิดเสียงจากจานชาม, ลดการเกาะตัวของหยดน้ำ และช่วยรักษาอุณหภูมิของน้ำ
- 820 x 430 x 228 มม.

มาตรฐาน

- คุณสมบัติตามมาตรฐาน
- ANSI A112.19.3M/CSA B45.4
- QB/T 4013

ข้อสังเกตสำหรับการติดตั้ง

ติดตั้งผลิตภัณฑ์โดยใช้คู่มือข้อแนะนำการติดตั้ง



ข้อมูลเฉพาะ

ผลิตภัณฑ์:	ซ้าย	ขวา
พื้นที่อ่าง	335 x 460 มม.	270 x 335 มม.
ระยะน้ำล้น	150 มม.	180 มม.
ขนาดรูท่อน้ำทิ้ง	38 หรือ 51 มม. (1-1/2" หรือ 2")	
*ระยะค่าโดยประมาณเพื่อเปรียบเทียบเท่านั้น		


ส่วนประกอบผลิตภัณฑ์	
ข้อต่อท่อน้ำทิ้งแบบลงพื้น	1200369
สะดืออ่าง	5163T-NA/1174273
อุปกรณ์ติดตั้ง	1127254
เชียง	1108778
ตะกร้าใส่ผัก	1108799
กระดาษแม่แบบ	1110885-X7

รุ่นผลิตภัณฑ์

รุ่น	ชื่อผลิตภัณฑ์	สี/วัสดุเคลือบผิว
K-3882X-F	อ่างล้างจาน สองหลุม รุ่นพอยท์	NA: ไม่ระบุ
แนะนำให้ใช้ร่วมกับผลิตภัณฑ์		
K-18006X	ก๊อกลงอ่างล้างจาน รุ่นนาทีโอ	CP: สีโครมเงา

ขนาดระยะแสดงค่าโดยประมาณ

หน่วย: มม.



ภาพแสดงผลิตภัณฑ์