

### KITCHEN SINK K-3883X

#### Features

- 304 stainless steel (Fabricated stainless steel)
- Undercounter
- Single basin
- Includes S-trap, overflow trap, quick flow strainer installation hardware, cutting board and wire basket
- Exceptional sound-absorption technology (SilentShield technology)
- 430 x 430 x 227 mm


#### Codes/Standards Applicable

Specified model meets or exceeds the following:

- ANSI A112.19.3M/CSA B45.4
- QB/T 4013

#### Installation Notes

Install this product according to the installation guide.



#### Technical Information

Fixture:	Basin area	Water depth
Sink	330 x 330 mm	150 mm
Drain hole	38 or 51 mm (1-1/2" or 2")	
*Approximate measurements for comparison only.		

Included components:	
S-trap	1200368
Strainer	5163T-NA
Fixing clips	1127254
Cutting board	1108778
Wire basket	1108799
Template	1110886-X7


#### Specified Model

Model	Description	Color/Finished
K-3883X-F	Poise kitchen sink	NA: None Applicable

Recommended Accessories		
K-15609X-4	Elate kitchen faucet	CP: Polished Chrome

Dimensions are approximate.

Unit: mm



#### Product Diagram

### อ่างล้างจาน K-3883X

#### คุณลักษณะ


- ผลิตจากสแตนเลสเกรด 304 (Fabricated stainless steel)
- แบบฝังใต้เคาน์เตอร์
- หนึ่งหลุม
- พร้อมข้อต่อน้ำทิ้งแบบลงพื้น, ท่อน้ำล้นในตัว, สะดืออ่างแบบควิกไฟว์, อุปกรณ์ติดตั้ง, เชียง และตะกร้า
- เทคโนโลยีไฮเลนซิลด์ ช่วยลดการเกิดเสียงจากงานขาม, ลดการเกาะตัวของหยดน้ำ และช่วยรักษาอุณหภูมิของน้ำ
- 430 x 430 x 227 มม.

#### มาตรฐาน

- คุณสมบัติตามมาตรฐาน
- ANSI A112.19.3M/CSA B45.4
- QB/T 4013

#### ข้อสังเกตสำหรับการติดตั้ง

ติดตั้งผลิตภัณฑ์โดยใช้คู่มือข้อแนะนำการติดตั้ง



#### ข้อมูลเฉพาะ

ผลิตภัณฑ์:	พื้นที่อ่าง	ระยาะน้ำลึก
อ่างล้างจาน	330 x 330 มม.	150 มม.
ขนาดรูท่อน้ำทิ้ง	38 หรือ 51 มม. (1-1/2" หรือ 2")	
*ระยาะค่าโดยประมาณเพื่อเปรียบเทียบเท่านั้น		

ส่วนประกอบผลิตภัณฑ์	
ข้อต่อท่อน้ำทิ้งแบบลงพื้น	1200368
สะดืออ่าง	5163T-NA
อุปกรณ์ติดตั้ง	1127254
เชียง	1108778
ตะกร้าใส่ผัก	1108799
กระดาษแม่แบบ	1110886-X7


#### รุ่นผลิตภัณฑ์

รุ่น	ชื่อผลิตภัณฑ์	สี/วัสดุเคลือบผิว
K-3883X-F	อ่างล้างจาน หนึ่งหลุม รุ่นพอยท์	NA: ไม่ระบุ

แนะนำให้ใช้ร่วมกับผลิตภัณฑ์		
K-15609X-4	ก๊อกผสมอ่างล้างจาน รุ่นอีเลท	CP: สีโครมเงา

ขนาดระยาะแสดงค่าโดยประมาณ

หน่วย: มม.



ภาพแสดงผลิตภัณฑ์