

### Features


- Vitreous china
- Undercounter
- With overflow
- Includes 52047 clamp assembly
- 489 x 413 x 191 mm [K-2210X]
- 540 x 438 x 191 mm [K-2211X]

### Codes/Standards Applicable

Specified model meets or exceeds the following:

- ASME A112.19.2/CSA B45.1
- TIS 791-2544

## UNDERCOUNTER LAVATORY K-2210X ALSO K-2211X



### Technical Information

Model	Drain hole	Water depth
K-2210X	44 mm	102 mm
K-2211X	44 mm	102 mm
Approximate measurements for comparison only.		

Included Components:	
Basin clamp assembly	52047
Cut-out template, K-2210X	1002975-X7
Cut-out template, K-2211X	1018997-X7

### Installation Notes

Install this product according to instruction in the cut-out template.

Supplied basin clamp assemblies require 25 mm minimum countertop thickness. Installer must supply anchors for thinner countertops.


**NOTICE:** Countertop manufacturer or cutter must use the cut-out template provided with the product, or a current one provided by Kohler Co. (call 0-2204-6222) Kohler Co. is not responsible for cutout errors when the incorrect cut-out template is used.

### Specified Model




Model	Description	Color/Finished
K-2210X	Caxton 17" undercounter lavatory	0: White
K-2211X	Caxton 19" undercounter lavatory	0: White

Recommended Accessory		
K-8998	P-trap	CP: Polished Chrome

Dimensions are approximate.  
Unit: mm



Model \ Dim	A	B	X	Y
K-2210X	436	354	489	413
K-2211X	480	381	540	438



Note: The recommended dimension for installation can be adjusted according to user preferences and layout.

### Product Diagram

### คุณลักษณะ

- สุขภัณฑ์เซรามิกประเภทวิทรีสไชน่า (Vitreous china)
- ติดตั้งแบบฝังใต้เคาน์เตอร์
- พร้อมรูน้ำล้น
- พร้อมชุดอุปกรณ์ยึดอ่างล้างหน้า รหัส 52047
- 489 x 413 มม. x 191 มม. [K-2210X]
- 540 x 438 มม. x 191 มม. [K-2211X]

### มาตรฐาน

- คุณสมบัติตามมาตรฐาน
- ASME A112.19.2/CSA B45.1
- มอก. 791-2544

### ข้อมูลเฉพาะ

สุขภัณฑ์	ขนาดรูสะดืออ่าง	ระยะน้ำล้น
K-2210X	เส้นผ่าศูนย์กลาง 44 มม.	102 มม.
K-2211X	เส้นผ่าศูนย์กลาง 44 มม.	102 มม.

\*ระยะค่าโดยประมาณเพื่อการเปรียบเทียบเท่านั้น

ส่วนประกอบสุขภัณฑ์	
ชุดอุปกรณ์ยึดอ่างล้างหน้า	52047
กระดาดแม่แบบ, K-2210X	1002975-X7
กระดาดแม่แบบ, K-2211X	1018997-X7


### รุ่นผลิตภัณฑ์

รุ่น	ชื่อผลิตภัณฑ์	สี/วัสดุเคลือบผิว
K-2210X	อ่างล้างหน้าฝังใต้เคาน์เตอร์ ขนาด 17 นิ้ว รุ่น แคชชั่น	0: สีขาว
K-2211X	อ่างล้างหน้าฝังใต้เคาน์เตอร์ ขนาด 19 นิ้ว รุ่น แคชชั่น	0: สีขาว


อุปกรณ์แนะนำ		
K-8998	ท่อน้ำทิ้งอ่างล้างหน้า	CP: สีโครมเงา

ขนาดระยะแสดงค่าโดยประมาณ


หน่วย: มม.




รุ่น	ระยะ	A	B	X	Y
K-2210X		436	354	489	413
K-2211X		480	381	540	438



การติดตั้งสำหรับเคาน์เตอร์หินอ่อน



การติดตั้งสำหรับเคาน์เตอร์ไม้



หมายเหตุ: ระยะแนะนำการติดตั้งสามารถปรับได้ตามความเหมาะสมของผู้ใช้งานและพื้นที่ติดตั้ง

### ภาพแสดงผลิตภัณฑ์

## อ่างล้างหน้าฝังใต้เคาน์เตอร์ K-2210X และ K-2211X

