



ROUGH-IN
Unit: Inch (cm)

1416193 Luxe plus vanity 750




1416178 Prologue plus vanity 750



- All dimensions are in Inch(cm).
- Fixture dimensions are nominal and conform to tolerances as per ASME Standard A112.19.2M.
- Product illustrations shown are representation only; actual products may vary.

COMPATIBLE VESSELS



TOOLS AND MATERIAL(Not supplied)


- Safety glasses
- Pencil
- Scissors
- Measuring tape
- Putty knife
- Plumbers putty
- Hack saw
- Keyhole saw or saber saw
- Drill bit as required
- Adjust able wrench
- Pipe wrench
- Tube cutter

Important Note:


- † Counter & Vessels not included with vanity.
- Refer vessel installation guideline for vessel installation.

INSTALLATION STEPS:


- 1 Paste the template on wall, check with spirit/bubble leveller. Drill M8 x8 holes for anti drop mounting system.
- 2 Take out both the drawers by pressing locks on either side of the bottom of the drawer.
- 3 Mount the furniture on the steel plates and level the furniture by adjusting screws in anti-drop mounting bracket. Check the level using bubble level in-built inside the product.



- 4 Place and slide the drawers over the slides. The drawers will lock automatically at the end position making a click sound.



ADJUSTMENT



KOHLER

CUT-OUT TEMPLATE / INSTALLATION INSTRUCTION
LUXE VESSEL VANITY 750MM (30459IN-*)
PROLOGUE VESSEL VANITY 750MM (30457IN-*)

BATHROOM FURNITURE

Thank you for choosing Kohler furniture. If installed and cared for as indicated, this piece will last for many years. The guarantee only applies to products that are installed and maintained according to the care and installation instructions below.

General Recommendations :

- Please check that the furniture has no defect prior to installation. Any complaint made regarding such an issue after installation will be rejected.
- Though Kohler cabinets are resistant to water and humidity but protection from water and humidity will increase the life of the product. Therefore, take care of the product as mentioned:
- As with any furniture with wood fiber panels, an overly-high level of humidity may damage the product. All furniture must be installed in a well-ventilated bathroom.
- Always use a shower door or curtain and wipe off splashes immediately.
- Any product likely to come into contact with water should be protected with a silicon-based seal product (i.e., in places where the product comes in contact with a tiled floor or is against a tiled wall). Wipe off water splashes immediately.
- If for any reason the furniture must be cut or drilled when installing, waterproof sharp edges with varnish or oil-based paint to prevent water seepage.
- After installation, remove all sawdust and clean drawer runners.
- Product should be installed by a skilled individual.
- Electrical connections (if any) should be performed by a qualified electrician, in compliance with the most recent local wiring regulations in effect, with particular attention to zones inside the bathroom.
- Note that products in wood veneer are natural and therefore all will differ. Natural wood is likely to change slightly in color with time due to exposure to UV rays. This is a natural process which is considered to be a part of the appeal and aesthetics of veneered wood, and lends a uniqueness to each product.

Daily care and use

- Dry off excess moisture with a towel or soft cloth, taking special care with the furniture edges.
- Never use detergents, bleach or abrasive cleaning products which could damage the product coating. Always test on a discrete area beforehand. Do not use wax-based polishing products which could alter the furniture's lacquer finish.
- Do not leave damp towel on the furniture. This could damage the product coating and cause mold or bacteria to proliferate.
- Do not lean against or hang on handles or doors.

Caution! Electric light-bulbs can get hot. Never touch them with wet hands. Always unplug the spotlight from the outlet before replacing a used light-bulb.

- When replacing a light-bulb, always use the appropriate type and strength. Use a cloth to avoid transferring grease spots to the new bulb and adversely affecting its performance.
- Never leave the furniture door directly open under a light fixture so heat will not accumulate.

Glass surfaces

- Do not strike the glass with a hard or sharp object.
- Do not place an extremely hot or cold object against or near glass surfaces except if a suitable thick, insulating material is used to prevent direct contact.
- If the glass is chipped or broken, replace it immediately. For further information about replacing glass or other components, please contact our technical departments.

Furniture Materials:

Glass (Mirror)

Description

This clear, hard, fragile, hygienic material is made from sand and potassium or sodium.

Daily care

Clean with a cloth as you would with any other glass surface.

Melamine and laminate

Description

Laminate: Coating made of layered brown paper sheets (often 3), covered with a sheet of decorative paper

glued to a wood conglomerate panel (made of wood fibers that are shredded, mixed with a binder and pressed).
Melamine: Layer of decorative paper glued to a wood conglomerate panel (made of wood fibers that are shredded, mixed with a binder and pressed).
Laminate is more resistant than melamine because of its thickness.
Melamine and laminate have hard, non-porous surfaces. They are therefore very hygienic and easy to clean.
Exposure to light (UV rays) may slightly alter nuances over time.

Daily care

Clean regularly with a paper towel, soft cloth (dry or damp) or a sponge (when damp cleaning, wipe well). Repeated use of household products for furniture, or waxing products may cause a sticky, unsightly layer to form. Refer to the installation instructions for general installation and care recommendations.

Specific stains

Light or recent stains: Dry or damp clean with paper towel, soft cloth or a sponge (when damp cleaning, wipe well).
Average or fairly old spots: Use extremely hot water and common, non-abrasive cleaning products (dish-washing liquid, soaps). Persistent or old spots: Apply dish-washing liquid or washing powder/water paste to spot overnight. If some spots persist, try solvents or weak acid (for scale).

Lacquer/Polyurethane gloss finish

Caution! This product has a film covering but this does not protect it against impacts. Proceed with care when assembling, and remove film after installation.

Description

Wood finish made from resin.
These polyurethane lacquers may have three different sheens: Gloss, satin or soft.
Though the polyurethane finish used on Kohler furniture is highly durable to UV, but over the years, they may start to discolor lightly as no finish is 100% UV resistant.

Daily care

Only use soapy water or a glass cleaner with a sponge; dry with a soft cloth. Note that PU/lacquered finishes can be easily scratched (resistant upto pencil hardness scratches) so always take care, particularly when cleaning

Specific stains

Recent stains or food stains: Clean with a soft cloth dipped in soapy water; then dry with a soft cloth.
Ballpoint pen or felt-tipped pen marks: Use rubbing alcohol. Test on a discrete location.
Nail polish: Carefully use acetone-free nail polish remover and a cotton swab for limited application. Test on a discrete area beforehand.

Wood veneer

Description

BWR Ply (Boiling Water Resistant) panel covered with a thin sheet of stained, varnished wood, which determines product appearance. Since this is a natural material, each piece is unique and differences in shades cannot be considered defects.
As opposed to solid wood, veneer will not change in shape; however, like all wood, it tends to acquire a patina over time from exposure to light (UV rays).

Daily care

Only use soapy water or a glass cleaner with a sponge; dry with a soft cloth.
Refer to the installation instructions for general installation and care recommendations.
Specific stains
Recent stains or food stains: Clean with a soft cloth dipped in soapy water; then dry with a soft cloth.
Ballpoint or felt-tipped pen marks: Use rubbing alcohol. Test on a discrete area of the furniture beforehand.
Nail polish: Carefully use acetone-free nail polish remover and a cotton swab for limited application. Test on a discrete area beforehand.

Solid wood

Description





Solid wood covered with a special anti-UV clear-coat lacquering/varnish. Smooth and even to the touch. Since this is a living material, each piece is unique, and therefore differences in shades can not be considered defects.
Common oak: Yellowish-white wood with a coarse grain and straight lines.

Daily use

Only use soapy water or a glass cleaner with a sponge; dry with a soft cloth.
Specific stains
Food stains: Clean with soapy water, rinse and dry with a soft cloth.
Natural clay powder is effective on grease stains.
Ballpoint or felt-tipped pen marks: Use rubbing alcohol or white spirits, lemon juice or an anti-rust product.
Nail polish: Carefully use acetone-free nail polish remover and a cotton swab for limited application. Test on a discrete area of the furniture beforehand.

Care and Cleaning Guidelines

- Always test your cleaning solution on an inconspicuous area on the product before applying it to the entire surface.
- Do not allow cleaners to sit or soak on the product.
- Use a soft, dampened sponge or cloth to clean. Never use abrasive material like a bristle brush or scouring pad.
- Wipe surfaces clean and rinse completely with water immediately after applying cleaners.



SPARE PART LIST

Luxe 750

| Part number | Description | Quantity |
|-------------|--|----------|
| 1416196 | Luxe vanity 750 Facia | - |
| 1416232 | Luxe Vanity 750- Bottom drawer (without facia) | - |
| 1416233 | Luxe Vanity 750- Bottom drawer (without facia) | - |
| 1416230 | 350mm slider assembly | - |
| 1416231 | 450mm slider assembly | - |
| 1416239 | Suspension bracket kit | - |
| 1346475 | Siphon Connectic (Valentine) - Bottle Trap | - |
| 1459700 | Drawer Matt | 1 |
| 1459701 | Drawer Matt | 1 |
| 1459704 | Drawer tray | 2 |
| 1459705 | Drawer tray | 1 |
| 1459706 | Bottom basket with lid | 1 |

Prologue 750

| Part number | Description | Quantity |
|-------------|--|----------|
| 1403301 | Prologue Vanity 750- bottom facia with handle | - |
| 1403304 | Prologue vanity 750- top facia with handle | - |
| 1416234 | Prologue Vanity 750- top drawer (without facia) | - |
| 1416179 | Prologue Vanity 750- bottom drawer (without facia) | - |
| 1416230 | 350mm slider assembly | - |
| 1416231 | 450mm slider assembly | - |
| 1416239 | Suspension bracket kit | - |
| 1346475 | Siphon Connectic (Valentine)- Bottle Trap | - |
| 1459700 | Drawer Matt | 1 |
| 1459701 | Drawer Matt | 1 |
| 1459704 | Drawer tray | 2 |
| 1459705 | Drawer tray | 1 |
| 1459706 | Bottom basket with lid | 1 |

- Contact us at:
Kohler India Corporation Pvt. Ltd.
6th Floor, Office Tower, Ambience Island,
NH-8, Gurugram, Haryana- 122001, INDIA.
Customer Care : (Monday-Saturday from 08:00am to 08:00pm)
Toll Free : 1800-103-2244) &
+91-124-4319685 / 86
Email : indiacustomer@kohler.com
Website: www.kohler.co.in
- For specific product warranty details logon to www.kohler.co.in/warranty for India.