


BEFORE YOU BEGIN



**WARNING:**  
Risk of personal injury or product damage. Handle with care.  
Vitreous China can break or chip if the bolts and nuts are over-tightened, or if the product is handled carelessly.

- Observe all local plumbing and building codes.
- Carefully inspect the new lav for any damage. In case of any damage, please discard the product & contact Kohler customer care.
- User should preserve this document to order spare parts in future.

TOOLS AND MATERIALS




ORDERNING INFORMATION

TRACE WSHB 55X40 1TAP H W/OV WHITE.....	K-30520IN-0	
TRACE PEDESTAL LAV.....	K-33932IN-0	TRACE HALF PED LAV.....K-33933IN-0
INCLUDES TRACE WSHB 55X40 1TAP H W/OV WHITE.....	K-30520IN-0	INCLUDES TRACE WSHB 55X40 1TAP H W/OV WHITE..... K-30520IN-0
INCLUDES BRIVE PLUS PEDESTAL.....	K-8705IN-0	INCLUDES BRIVE+™ HALF PEDESTAL ONLY..... K-5584IN-0

ROUGHING-IN

Unit: Inches (cm)

30520IN-0



- NOTES:**
- Fixture dimensions are nominal and confirm to tolerances as per ASME Standard A112.19.2M.
  - Product illustrations shown are representative only; actual product may vary.
  - Kohler reserves the right to make changes in product characteristics, packaging or availability at any time without notice.

CAUTION : Do not use white cement or high lime-content cement to install this lav. The expansion of cement due to rise in temperature may cause the lav to crack or be damaged. Kohler is not responsible for any damage due to installation with the use of cement.

WALL-MOUNT LAVATORY INSTALLATION INSTRUCTIONS

1

Finished Wall  
7 cm  
Plastic Anchor  
Metal Stud

Ø14mm

A  
C/L  
B  
C/L

NOTE: Refer Roughing-in for dimensions A & B

2

NOTE: Refer manufacturer's Installation Instruction for Installation of Faucet, Drain & Bottle Trap with lavatory.

3

4

HALF-PEDESTAL INSTALLATION INSTRUCTIONS

1

Bottom View of Lavatory

2

3

FULL-PEDESTAL INSTALLATION INSTRUCTIONS

1

Bottom View of Lavatory

2

3

4


5

6


Recommended Bottle Trap

Recommended Drain


Recommended Spare Parts



K-75823IN-\*\*/  
K-7314IN-\*\*



K-45432IN-\*\*



1223187  
Mounting Kit

\*\*Finish code must be specified when ordering.