

Features

- Fluid and aerodynamic form with thin ceramic of 7 mm.
- Recessed drain with a drain cover.
- Germshield™ Technology, Anti-microbial ceramic provides protection against Virus, Bacteria & other germs.
- No core-cutting required, drain-cut only.
- Superior Glaze: Long lasting, durable glaze easy to clean surface, resistant to chemicals and stains.
- Optimum Depth to contain Splashes.

Product Details

- Material: Vitreous China
- Overflow: Without Overflow Hole

Required Accessories

- Bottle Trap (75823IN-*/ 7314IN-**).

Spare Part Information

- Drain Lid Assy: 1396354-**
- Drain Assy: 1428877-**

Ordering Information

NYSA Lav In White.....K-31343IN-SS-**

Package Content

1 Drain Assembly, 1 Installation Template & 1 Warranty Card.



COMPATIBLE FAUCETS	
SKU CODE	PRODUCT DESCRIPTION
72337IN-4ND-**	Aleo+ Tall Lav Faucet W/O Drain
20071IN-4-**	Aleo+ Pillar Tap, Tall
5684IN-4ND-**	Aleo+ WM Lav Faucet Trim
72298IN-4ND*	Aleo Tall Lav Faucet W/O Drain
20070IN-4-**	Aleo Pillar Tap, Tall
5683IN-4ND-**	Aleo WM Lav Faucet Trim
24845IN-4ND-**	Elate® SC WM Lav Faucet Trim
24846IN-4ND-**	Elate® Cold Only Faucet Trim
22535IN-4ND-**	Hone® SC Tall Lav Faucet W/O Drain
22539IN-4-**	Hone® Tall Pillar Tap
22540IN-4ND-**	Hone® SC WM Lav Facuet W/O Drain
23475IN-4ND-**	Parallel™ SC Tall Lav W/o Drain
23483IN-4-**	Parallel Tall Pillar Tap
23486IN-4ND-**	Parallel WM SC Lav Faucet
37329IN-4ND-**	Strayt® SC Tall Lav Faucet W/O Drain
37334IN-4-**	Strayt® Tall Pillar Tap
23967IN-4ND-**	Vive SC Tall Lav Faucet W/O Drain
23975IN-4ND-**	Vive SC Monoblock WM Lav Faucet W Valve

**Finish code must be specified when ordering.


KOHLER® Ten-Year Limited Warranty

See website for detailed warranty information
www.kohler.co.in/warranty

Available Colour/Finishes

Colour tiles intended for reference only.

Colour	Code	Description
	0	White



Technical Specification

All product dimensions are nominal.

Lavatory configuration	Single
Installation	Above Counter
Lav area	Length: 24-13/16" (63cm) Width: 16-7/16" (41.8cm) Height: 5-3/8" (13.7cm)
Drain hole	Ø1-3/4" (4.4cm)
Template	1423199-IN7

Notes

Install this product according to the installation guide.

Choose a faucet that will provide adequate clearance and will direct the water stream to the center of the bathroom sink.