


**Features**

- Metal construction
- One-piece, self-contained ceramic disc valve allows both volume and temperature control
- Temperature memory allows faucet to be turned on and off at any temperature setting
- High-temperature limit setting for added safety
- Three-function sprayhead with spray, aerated stream, and pause settings
- Promotion™ technology with nylon hose and ball joint for easy operation
- Lever handle
- Contemporary styling
- 360° spout rotation
- 9" (229 mm) or 8" (203 mm) swing spout reach
- Lower flow aerator options available (refer to the Kohler Price Book)
- 2.2 gallons (8.3 L) per minute maximum flow rate


**PULL-OUT KITCHEN SINK FAUCET**

**K-6331**  
**ALSO K-6332**

**ADA**



**K-6331**



**K-6332**

**Codes/Standards Applicable**

Specified model meets or exceeds the following at date of manufacture:

- ADA
- ASME A112.18.1/CSA B125.1
- ICC/ANSI A117.1
- Energy Policy Act of 2005
- NSF 61
- All applicable US Federal and State material regulations

**Colors/Finishes**

- CP: Polished Chrome
- Other: Refer to Price Book for additional colors/finishes

**Specified Model**

Model	Description	Colors/Finishes
K-6331	Pull-out kitchen sink faucet – 9" (229 mm) spout reach	<input type="checkbox"/> CP <input type="checkbox"/> Other ____
K-6332	Pull-out kitchen sink faucet – 8" (203 mm) spout reach	<input type="checkbox"/> CP <input type="checkbox"/> Other ____

**Product Specification**


The contemporary pull-out kitchen sink faucet shall be of metal construction. Product shall have a maximum flow rate of 2.2 gallons (8.3 L) per minute with lower flow aerator options available (refer to the Kohler Price Book). Product shall feature a one-piece, self-contained ceramic disc valve, allowing volume and temperature control. Product shall feature temperature memory, allowing the faucet to be turned on and off at any temperature setting. Product shall feature a high-temperature limit setting for added safety. Product shall feature a 360° spout rotation. Product shall feature a three-function sprayhead with spray, aerated stream, and pause settings. Product shall feature Promotion technology with nylon hose and ball joint for easy operation. Product shall be available with a 9" (229 mm) or 8" (203 mm) swing spout reach. Pull-out kitchen faucet shall be Kohler Model K-\_\_\_\_\_-\_\_\_\_\_.

# EVOKE™

## Installation Notes

Install this product according to the installation guide.

**ADA** compliant when installed to the specific requirements of the regulation.



**Product Diagram**