


**PULL-OUT KITCHEN SINK FAUCET  
K-7505  
ALSO K-7506**

ADA

**Features**

- Metal construction
- One-piece, self-contained ceramic disc valve allows both volume and temperature control
- Temperature memory allows faucet to be turned on and off at any temperature setting
- Promotion™ technology with nylon hose and ball joint for easy operation
- Contemporary styling
- Three-function sprayhead with spray, laminar flow, and pause settings
- 360° spout rotation
- 8" (203 mm) or 7" (178 mm) spout reach
- 1.8 gallons (6.8 L) per minute maximum flow rate at 60 psi (4.1 bar)
- Meets CalGreen requirements for kitchen faucets



**Codes/Standards Applicable**

Specified model meets or exceeds the following:

- ADA
- ASME A112.18.1/CSA B125.1
- ICC/ANSI A117.1
- Energy Policy Act of 2005
- NSF 61
- All applicable US Federal and State material regulations

**Colors/Finishes**

- CP: Polished Chrome
- Other: Refer to Price Book for additional colors/finishes

**Accessories**

- NA: None applicable

**Specified Model**

Model	Description	Colors/Finishes	
K-7505	Pull-out kitchen sink faucet – 8" (203 mm) spout reach	<input type="checkbox"/> CP	<input type="checkbox"/> Other _____
K-7506	Pull-out kitchen sink faucet – 7" (178 mm) spout reach	<input type="checkbox"/> CP	<input type="checkbox"/> Other _____

Optional Accessories		
1012715	Deep rough-in kit	<input type="checkbox"/> NA
1055715	Low flow kit – reduces maximum flow to 1.5 gpm (5.7 L) at 60 psi (4.1 bar)	<input type="checkbox"/> NA

**Product Specification**


The contemporary pull-out kitchen sink faucet shall be of metal construction. Product shall have a maximum flow rate of 1.8 gallons (6.8 L) per minute with lower flow aerator options available (refer to the Kohler Price Book). Product shall feature a one-piece, self-contained ceramic disc valve, allowing volume and temperature control. Product shall feature temperature memory, allowing the faucet to be turned on and off at any temperature setting. Product shall feature a 360° spout rotation. Product shall feature a three-function sprayhead with spray, laminar flow, and pause settings. Product shall feature Promotion technology with nylon hose and ball joint for easy operation. Product shall be available with a 8" (203 mm) or 7" (178 mm) spout reach. Product shall meet CalGreen requirements for kitchen faucets. Pull-out kitchen faucet shall be Kohler Model K-\_\_\_\_\_-\_\_\_\_\_.

# PURIST®

## Installation Notes

Install this product according to the installation guide.

**ADA** compliant when installed to the specific requirements of these regulations.



**Product Diagram**