

KOHLER® Faucets Showerhead and wireless speaker with Amazon Alexa

Moxie®
K-28238-NKA

Features

- Full-coverage spray produces an encompassing spray ideal for everyday use.
- Best-in-class audio with sound by Harman Kardon®.
- Easily toggle between two sound-performance settings, "Shower" and "Normal," depending upon where speaker is being used.
- IPX7-rated waterproof speaker.
- Magnetic showerhead holds speaker securely in place, yet removes easily for charging.
- Built-in microphones tune out background noise for clearer voice command detection.
- Featuring BLUETOOTH wireless technology, allowing you to pair any compatible device to stream your favorite music, podcast, or other audio content.
- Amazon Alexa-enabled speaker allows for voice control to play music, hear the news, check weather, and more.
- Wireless speaker can be used outside the shower space, independent of the showerhead, to stream music in any room.
- Speaker provides up to five-and-a-half hours of play time.
- Charging dock quickly and easily charges speaker.
- Download the KOHLER Konnect® app for additional functionality.
- 2.5 gpm (9.5 lpm) maximum flow rate at 80 psi (5.5 bar).

Material

- Durable material construction.
- KOHLER finishes resist corrosion and tarnishing.

Installation

- Wall-mount.
- Shower arm and flange sold separately.

Required Products/Accessories

K-7395 Shower Arm and Flange

Included Components

Additional Components:

Alexa speaker(Qty: 1)
Charging cable(Qty: 1)
Charging dock(Qty: 1)
Showerhead(Qty: 1)



Codes/Standards

ASME A112.18.1/CSA B125.1
DOE - Energy Policy Act 1992




KOHLER® One-Year Limited Warranty KOHLER® Faucet Lifetime Limited Warranty

See website for detailed warranty information.

The BLUETOOTH® word mark and logos are registered trademarks owned by Bluetooth SIG, Inc. and any use of such marks by Kohler Co. is under license. Other trademarks and trade names are those of their respective owners.

Available Colors/Finishes

Color tiles intended for reference only.


Color	Code	Description
	CP	Polished Chrome
	BN	Vibrant® Brushed Nickel
	BL	Matte Black

1-800-4KOHLER (1-800-456-4537)

Kohler Co. reserves the right to make revisions without notice to product specifications.
For the most current Specification Sheet, go to www.kohler.com.

THE BOLD LOOK
OF **KOHLER®**

KOHLER Faucets Showerhead and wireless speaker with Amazon Alexa
Moxie®
K-28238-NKA



Technical Information

All product dimensions are nominal.
 Power source: Battery - DC, not included
 Electrical component rating: Speaker: 10 W
 Amplifier channels: 1 at 10 W per channel
 Charge time: 3 hours
 Usage time: 5 hours
 Bluetooth® range: 32.8 ft (0.8 m)
 Bluetooth® version: 5.0
 Max. Ambient temp: 140°F (60°C)
 Signal to noise ratio: >70 dB

Showerhead/Body Spray:

Rated maximum flow: 2.5 gal/min (9.5 l/min)
 Pressure: 80 psi (5.5 bar)

Notes

Install this product according to the installation instructions.
 Follow local building electrical codes.
 A Bluetooth® wireless device is required to stream music
 For use with automatic compensating valves rated at 2.00 gal/min (7.6 L./min) or less.