

Modulo Universal Concealed Box

98699D

Product Description: Modulo universal concealed box

Product Dimensions: W139 x H184 mm

Material: Forged Brass Body

Minimum Pressure: 0.5 bar

Product Weight (kg): 2.0

Fixings Included: Yes

Guarantee (Years): 5

Required Items:	98730D-CP	Aleo thermo. built-in single sequential shower valve with 2 way diverter
	98726D-CP	Aleo thermostatic built-in shower valve with temperature & flow control
	98734D-CP	Aleo built-in 3-Way diverter valve
	98731D-CP	Cuff thermo. built-in single sequential shower valve with 2 way diverter
	98727D-CP	Cuff thermostatic built-in shower valve with temperature & flow control
	98735D-CP	Cuff built-in 3-Way diverter valve
	98733D-CP	Strayt thermo. built-in single sequential shower valve with 2 way diverter
	98729D-CP	Strayt thermostatic built-in shower valve with temperature & flow control
	98737D-CP	Strayt built-in 3-Way diverter valve
	98701D-NF	Recess kit for deeper wall installation 130 -150 mm
	98700D-CP	Recess kit for thin wall installation (1 hole) 67 -80 mm
	98789D-CP	Recess kit for thin wall installation (2 hole) 67 -80 mm



- Additional Information:**
- Simple installation with no special tools needed
 - 100% waterproof and reduces noise levels
 - Thermostatic valve limits water temperature to a maximum of 50°C for safety
 - Simple maintenance if required to change the valve after installation
 - Flexibility for installation depth from 80 mm - 110 mm
 - Trim Installation plates are equipped with a 'Breathing Channel' that avoids condensation inside the Modulo box
 - Leaking avoided due to perfect seal provided by box's plastic envelope
 - Integrated level: easy box positioning
 - Easy maintenance: direct access to valve servicing parts by removing trim
 - Can be installed on different surfaces: walls in concrete, plaster, wood, industrial partitions
 - Option to switch from mechanical to thermostatic mode, thanks to easy valve and trim change
 - Box cover with prongs to use as cut out template
 - Connector available to annex two Modulo universal boxes

Kohler UK

Sales and Technical:

+44 (0) 844 571 0048 (Calls cost 7p per minute plus your phone company's access charge)

info@kohler.co.uk


www.KOHLER.co.uk

THE BOLD LOOK
OF **KOHLER**®

Modulo Universal Concealed Box

98699D

Dimensions (mm)




Features

Durable
Forged brass resists wear and leaks

Universal Box
Works with valves shown below for multiple shower installations

Easy Installation
An integrated spirit level and bracket ensure the box is properly aligned

Pre-Install Option
Install Modulo and choose valve-trim at your convenience or easily change at a later time



Valve options

- Thermostatic built-in single sequential shower valve with 2 way diverter
- Thermostatic built-in shower valve with temperature & flow control
- Built-in 3-way diverter valve

Choose from the three trim styles below:



Aleo



Cuff



Strayt