


Skyline Walk-In Enclosure



These instructions must be left with the user

Installation Guide

THE BOLD LOOK
OF **KOHLER**®

INTRODUCTION

Thank you for purchasing a quality KOHLER® product. To enjoy the full potential of your new product, please take time to read this guide thoroughly, having done so, keep it handy for future reference.

The following pages aim to provide comprehensive installation instructions, plus advice on how to care and maintain your product.

We recommend that the unit is installed by a qualified plumber or engineer.

General

1. Read all of these instructions and retain this guide for later use.
2. Pass on this guide in the event of change of ownership of the installation site.
3. Follow all warnings, cautions and instructions contained in this guide.
4. Remove all protective tape from the enclosure before installation.

GENERAL INFORMATION

Safety Information

1. Care should be taken when drilling into walls and floors to avoid any hidden pipes or wires.
2. We strongly recommend that all glass panels are moved by a minimum of two people and that any protective packaging along the glass edges is kept in place for as long as possible to prevent damage before installation.
3. During installation we recommend additional help in lifting heavy doors and side panels.
4. Wear protective footwear when lifting panels.
5. Wear safety glasses when drilling.

Wall Preparation



The wall channels must be installed onto a tiled or waterproof finished flat and even wall surface. Failure to do so will result in an unsatisfactory seal, which may cause property damage.



GUARANTEE


For **domestic installations**, your enclosure has the benefit of our lifetime guarantee which starts from date of purchase.

For **non-domestic installations**, we guarantee the product against any defect in materials or workmanship for a period of one year from the date of purchase.

For terms and conditions refer to the back cover of this guide.

Recommended Usage	
Domestic	✓
Light Commercial	✓
Heavy Commercial	✗
Healthcare	✗

PACK CONTENTS



INSTALLATION

The tray should be fitted and the walls tiled before installation of the enclosure.

Mark the position of the wall channel from the wall tiles on the back wall.

745mm (1400 tray)
640mm (1700 tray)


(adjust the dimension
if other than
10mm tile thickness)

NOTE:
LH VERSION
SHOWN.
RH FITTING
MIRRORS THE
INSTALLATION
SHOWN.

Back edge of
wall
channel

STEP 1


Fit the curved panel wall channel to the wall.




Place the glass mounting block into the tray.

IMPORTANT

Do not remove the adhesive backing from the underside of the mounting block at this stage.



Carefully lift the glass into place. The jamb fits onto the wall channel and the bottom corner of the glass fits into the mounting block (see Step 5).



Carefully slide the jamb onto the wall channel.


Jamb

Wall channel


Place the corner of the glass into the mounting block.

STEP
5

Adjust the glass until it is vertical and equally spaced around the lip of the tray.




Mark the position of the mounting block on the tray.




STEP
6

Carefully remove the curved panel from the tray.
Remove the mounting block.

Remove the backing paper from the mounting block.




Fit the mounting block to the marks on the tray.
Place a blob of sealant into the mounting block.




STEP
7

Carefully lift the curved panel back into place and check that the glass is vertical and equally spaced around the lip of the tray.




STEP 8

Drill 3 x 3mm holes through the jamb into the wall channel.



Secure the jamb to wall channel with 3 x screw B.




STEP 9

Mark the fixing point for the lintel on the wall at the height of the top of the glass.

984mm (1400 tray)
1240mm (1700 tray)


(adjust the dimension if other than 10mm tile thickness)






STEP 10




Loosely fit the parts of the lintel together.

Note: the lintel end with a straight section goes towards the wall.




STEP 11







Remove the backing paper from the mounting block.




Fit the mounting block to the tray.
 Note: The slot for the glass should face the wall channel. Place a blob of sealant into the mounting block.




Carefully lift the side panel into position, uncoated side to the outside.



Carefully slide the jamb onto the wall channel.




At the other end, place the glass into the mounting block.




Ensure the glass panel is vertical.

Drill 3 x 3mm holes through the wall channel into the jamb.



Secure glass panel with 3 x screw B.


Fit the towel rail to the glass panel.



Note:
Towel rail can be fitted
inside or outside
of the enclosure


**STEP
22**

With the panel vertical and the towel rail
horizontal, mark the position of the wall mount
on the wall.




**STEP
23**

Remove the towel rail and remove the wall mount.
Place on the wall as marked. Mark the fixing
hole on the wall.




Drill a 6mm hole
in the wall.



Fit plug.




Secure the
wall mount.




**STEP
24**




Push the towel rail into the wall mount and re-fit
the towel rail to the glass (see Step 22).



Adjust the glass panel so that it is vertical.
Tighten the grub screw to secure the towel rail.



**STEP
25**



MAINTENANCE

General Maintenance

Providing the shower enclosure has been correctly installed and is operated in accordance with the instructions contained in this guide, difficulties should not arise.

If any maintenance is required then it must be carried out by a competent tradesperson to whom the maintenance instructions are provided.

Before replacing any parts ensure the underlying cause of the malfunction has been resolved.

Cleaning

Warning! Many household cleaners contain abrasive and chemical substances and should not be used for cleaning painted, plated or plastic fittings.

These finishes should be cleaned with a mild washing up detergent or soap solution and then wiped dry using a soft cloth.

Care

To preserve the beauty of your shower enclosure for many years, please observe the following care instructions:

Rinse glass and frame with clear water after showering. Remove water droplets with a squeegee. Do not rub dry! To clean your shower hygienically and easily, we recommend the use of a biodegradable cleanser.

Regular cleansing with a biodegradable cleanser prevents stubborn stains and ensures a clean and hygienic surface for many years. Do not use scouring or caustic cleansers under any circumstances! These can damage the surface of the frame, glass and decorative parts as well as the plastic parts.

Chrome Parts

Use only cleansers expressly specified for chrome!

NOTES

CUSTOMER SERVICE

Guarantee

Your enclosure has the benefit of our lifetime guarantee which starts from the date of purchase.

To activate this guarantee, you must return your completed registration card with a copy of proof of purchase from an approved Kohler retailer within 30 days of purchase.

This guarantee is in addition to your statutory rights and is subject to conditions (see registration card).

What to do if something goes wrong

If your product does not function correctly when you first use it, contact your installer to check that it is installed in accordance with the instructions in this manual.

If this does not resolve the issue, contact our Customer Services Team who will offer you or your installer help and advice.



Helpdesk Service

Our Customer Services Team is comprehensively trained and can offer help and advice, spare parts, accessories or a service visit.

We will need you to have your model name, model number and date of purchase.



KOHLER® Website (www.KOHLER.co.uk)

From our website you can download additional user guides or request a service visit.



Spares and Accessories

We hold the largest stocks of genuine Kohler spares and accessories.

Contact us for a price and to purchase spares or accessories.



Service / Repairs

No one knows our products better than our nationwide team of Service Technicians. We can carry out service or repair work to your product both during and after the guarantee period.

Ask about our fixed price service repairs.

To Contact Us: UK



0844 571 0048



Fax: 0844 571 7157



E-mail: info@kohler.co.uk

To Contact Us: Eire Only



0044 844 571 0048



Fax: 0044 844 571 7157

By Post:

Kohler Mira Limited
Customer Services Dept,
1 Penrose Place,
Skelmersdale,
WN8 9PR



Kohler Mira Limited, Cromwell Road, Cheltenham,
Gloucestershire, GL52 5EP, UK

13

EN 14428:2004 + A1: 2008

Kohler is a registered trade mark.
The company reserves the right to alter
product specifications without notice.

THE BOLD LOOK
OF **KOHLER®**