



Mira Flight Safe Rectangle Shower Trays

Mira Flight Low height flat top or upstands



Mira Flight Safe tray - rectangle



Dimensions

All sizes are in mm

Size	Upstands	Trays product code	Riser conversion kit product code
900X760	0	1.1697.017.AS	1.1697.030.WH
900X760	4	1.1697.351.AS	1.1697.030.WH
1000X700	0	1.1697.045.AS	1.1697.033.WH
1000X760	0	1.1697.008.AS	1.1697.033.WH
1000X800	0	1.1697.007.AS	1.1697.033.WH
1000X800	4	1.1697.456.AS	1.1697.033.WH
1100X800	0	1.1697.013.AS	1.1697.033.WH
1200X700	0	1.1697.046.AS	1.1697.033.WH
1200X760	0	1.1697.006.AS	1.1697.033.WH
1200X760	4	1.1697.345.AS	1.1697.033.WH
1200X800	0	1.1697.005.AS	1.1697.033.WH
1200X800	4	1.1697.348.AS	1.1697.033.WH
1200X900	0	1.1697.018.AS	1.1697.033.WH
1200X900	4	1.1697.490.AS	1.1697.033.WH
1400X700	0	1.1697.047.AS	1.1697.034.WH
1400X760	0	1.1697.004.AS	1.1697.034.WH
1400X800	0	1.1697.019.AS	1.1697.034.WH
1400X900	0	1.1697.042.AS	1.1697.034.WH
1500X700	0	1.1697.048.AS	1.1697.034.WH
1500X760	0	1.1697.003.AS	1.1697.034.WH
1600X700	0	1.1697.020.AS	1.1697.034.WH
1600X760	0	1.1697.002.AS	1.1697.034.WH
1600X900	0	1.1697.043.AS	1.1697.034.WH
1700X700	0	1.1697.021.AS	1.1697.034.WH
1700X760	0	1.1697.001.AS	1.1697.034.WH
1700X900	0	1.1697.044.AS	1.1697.034.WH

Dimensions (mm)											
Flat top						Upstands					
A	B	C	D	E	F	A	B	C	D	E	F
900	760	165	68	40	140-160	910	770	170	72	62	162-182
1000	700	165	68	40	140-160	-	-	-	-	-	-
1000	760	165	68	40	140-160	1010	770	170	72	62	162-182
1000	800	165	68	40	140-160	1010	810	170	72	62	162-182
1100	800	165	68	40	140-160	-	-	-	-	-	-
1200	700	165	68	40	140-160	-	-	-	-	-	-
1200	760	165	68	40	140-160	1210	770	170	72	62	162-182
1200	800	165	68	40	140-160	1210	810	170	72	62	162-182
1200	900	165	68	40	140-160	1210	910	170	72	62	162-182
1400	700	165	68	40	140-160	-	-	-	-	-	-
1400	760	165	68	40	140-160	-	-	-	-	-	-
1400	800	165	68	40	140-160	1410	810	170	72	62	162-182
1400	900	165	68	40	140-160	1410	910	170	72	62	162-182
1500	700	165	68	40	140-160	-	-	-	-	-	-
1500	760	165	68	40	140-160	-	-	-	-	-	-
1600	700	165	68	40	140-160	-	-	-	-	-	-
1600	760	165	68	40	140-160	-	-	-	-	-	-
1600	900	165	68	40	140-160	-	-	-	-	-	-
1700	700	165	68	40	140-160	-	-	-	-	-	-
1700	760	165	68	40	140-160	1710	770	170	72	62	162-182
1700	900	165	68	40	140-160	1710	910	170	72	62	162-182

To download other resources, and for more information and advice on our products just visit:
www.mirashowers.co.uk

