



Tranquility®

60" whirlpool with apron and drain end pump
66050101



Features

- 18-1/8" apron, 11-1/4" soaking depth.
- End drain can be installed as left- or right-hand drain.
- Six color-matched hydromassage jets with adjustable flow control.

Material

- Made from solid Vikrell® material for strength, durability, and lasting beauty.

This product has been discontinued.

Installation

- Drop-in or alcove.

Included Components

Product consists of:

- 66051101 60" whirlpool with drain end pump
- 61058100 60" x 42" bath apron only



DISCONTINUED

ADA

This product has been discontinued.

Codes/Standards

- ASME A112.19.7/CSA B45.10
- CSA B45.5/IAPMO Z124
- ASTM E162
- ASTM E662
- UL 1795
- ADA
- ICC/ANSI A117.1
- EPA TSCA Title VI

DISCONTINUED

Warranty – Bathing Fixtures (and Kitchen and Utility Sinks Made of Solid Vikrell® Material)


See website for detailed warranty information.

1-800-STERLING (1-800-783-7546)

Kohler Co. reserves the right to make revisions without notice to product specifications.

For the most current Specification Sheet, go to www.sterlingplumbing.com.

3-20-2020 08:07 - US



Required Electrical Service

One dedicated circuit required, protected with Class A Ground-Fault Circuit-Interrupter (GFCI). Outside North America, this device may be known as a Residual Current Device (RCD).

Pump: 120 V, 15 A, 60 Hz

Technical Information

All product dimensions are nominal.

Installation: Drop-in, Three-wall alcove

Drain location: End

Basin area, bottom: 42" x 23" (1067 mm x 584 mm)

Basin area, top: 51" x 32-1/2" (1295 mm x 826 mm)

Water depth: 11-1/4" (286 mm)

Water capacity: 56 gal (212 L)

Electrical component rating: Pump: 120 V, 7 A, 60 Hz

Pump speed: Single

Minimum flat for door: 1-1/4" (32 mm)

Notes

Install this product according to the installation instructions.

Provide one grounded electrical outlet within 24" (610 mm) of each component.

Pump is supplied with 24" (610 mm) grounding-type plug-in cord. Locate the outlet behind the whirlpool, and within 24" (610 mm) of the pump.

Pump service access is required.

Do not disassemble the pump or piping as this could void the warranty.

Size the drain cutout to fit the drain assembly that will be used.

End stud positioning is critical if nailing-in flanges are to be used.

Double-studding is recommended for pivot shower door installations.

Studs should be positioned roughly as shown for support clip or roofing nail installation.

ADA compliant when installed to the specific requirements of these regulations.