



# Accord® Smooth

60" x 30" Vikrell® bath/shower with Aging in Place  
backerboards, right above-floor drain  
**71240128**



## Features

- 17-1/4 (438 mm) apron
- Snap-together modular design
- Smooth, high-gloss walls
- Four corner shelves
- Aging in Place backerboards
- 3" (76 mm) drain-to-floor clearance for above-floor drain installation

## Material

- Made from solid Vikrell® material for strength, durability, and lasting beauty

## Installation

- Alcove
- Right drain
- Caulk-free installation

## Recommended Products/Accessories

- 71247103 30" ADA adaptable smooth bath/shower grab bar kit
- 71147104 30" bath seat kit
- K-23726 Drain treatment
- K-23733 Vikrell® cleaner

## Included Components

- 71244106 60" x 30" Vikrell® bath wall set with Aging in Place backerboards
- 71141128 60" x 30" Vikrell® bath, right above-floor drain



## Codes/Standards

- CSA B45.5/IAPMO Z124
- ASTM E162
- ASTM E662
- HUD, UM Bulletin 73
- IAPMO Certification


## STERLING® Vikrell® or Acrylic Baths and Shower Bases Ten-Year Limited Warranty

See website for detailed warranty information.


## Available Colors/Finishes

*Color tiles intended for reference only.*

### Color Code Description

	0	White
---	---	-------

**Accord® Smooth**  
60" x 30" Vikrell® bath/shower with Aging in Place  
backerboards, right above-floor drain  
**71240128**



**Technical Information**

All product dimensions are nominal.

Drain location:	Right
Basin area, bottom:	46-1/4" x 20-1/2" (1175 mm x 521 mm)
Basin area, top:	52-1/4" x 22-1/2" (1327 mm x 572 mm)
Water depth:	11" (279 mm)
Water capacity:	34 gal (128.7 L)
Maximum door height:	56-1/2" (1435 mm)
Maximum door width:	56-3/4" (1441 mm)

**Notes**

Install this product according to the installation instructions.

Product is designed to be used with a single-hole mixer valve with an escutcheon cover not to exceed 7-3/4" (197 mm) in width.

Studs should be positioned roughly as shown. Bath cannot be installed without the wall surround.

Width shifts from 60" (1524 mm) at front to 59-3/8" (1508 mm) at back. Use 1/4" (6 mm) furring strips at back for drywall over nailing-in flange installation.

ADA adaptable when grab bars and seat are installed per the specific requirements of these regulations.

For future ADA compliance, select a mixing valve location that will not interfere with a control wall grab bar.