



**Accord®**

60" shower stall with Aging in Place grab bars  
**72270103-N**



**Features**

- Tongue-and-groove modular design allows for easy installation during any phase of construction.
- 3-1/2" threshold.
- Geometric back wall design with convenient shelves for ample storage.
- Easy to clean, durable high-gloss finish.
- Includes three Aging in Place Nickel grab bars (one 80012031 and two 80001024).

**Material**

- Compression molded from our exclusive solid Vikrell® material.

**Installation**

- Alcove.
- Caulk-free installation.
- Center drain.

**Recommended Products/Accessories**

- 5475-59 Frameless sliding shower door
- 5477-59 Frameless sliding shower door
- 5970-59 Framed sliding shower door
- 5975-59 Framed sliding shower door
- 5976-59 Framed sliding shower door
- 5977-59 Framed sliding shower door
- 547808-59 Frameless sliding shower door
- 572075-59 Framed sliding shower door
- 581075-59 Frameless sliding shower door
- K-23726 Drain treatment
- K-23723 Faucet cleaner
- K-23733 Vikrell® cleaner

**Included Components**

- Product consists of:
- 72245103-N 36" end wall set with Aging in Place grab bars
  - 72271100 60" x 36" shower base
  - 72272103-N 60" shower back wall with Aging in Place grab bars



**Codes/Standards**

- CSA B45.5/IAPMO Z124
- ASTM E162
- ASTM E662
- HUD, UM Bulletin 73



**Warranty – Bathing Fixtures (and) Kitchen and Utility Sinks Made of Solid Vikrell® Material**

**STERLING® Warranty - Grab Bars**

See website for detailed warranty information.

**Available Colors/Finishes**

*Color tiles intended for reference only.*


Color	Code	Description
	0	White
	96	KOHLER Biscuit

1-800-STERLING (1-800-783-7546)

Kohler Co. reserves the right to make revisions without notice to product specifications.

For the most current Specification Sheet, go to [www.sterlingplumbing.com](http://www.sterlingplumbing.com).

8-22-2020 13:57 - US



### Technical Information

All product dimensions are nominal.

Installation:	Three-wall alcove
Drain location:	Center
Drain hole diameter:	3-5/16" (84 mm)
Minimum flat for door:	3-1/4" (83 mm)
Threshold height:	3-1/2" (89 mm)
Maximum door height:	72" (1829 mm)
Maximum door width:	56-5/8" (1438 mm)

### Notes

- Install this product according to the installation instructions.
- Studs should be positioned roughly as shown. Double studding is recommended for pivot shower door installations.
- Attach grab bars at the specified backerboard locations only.
- Shower base cannot be installed without the wall surround.