



Accord®

60" shower stall with Aging in Place grab bars

72270103-V



Features

- Tongue-and-groove modular design allows for easy installation during any phase of construction.
- 3-1/2" threshold.
- Geometric back wall design with convenient shelves for ample storage.
- Easy to clean, durable high-gloss finish.
- Includes three Aging in place Matte Silver grab bars (one 80012031 and two 80001024).

Material

- Compression molded from our exclusive solid Vikrell® material.

Installation

- Alcove.
- Caulk-free installation.
- Center drain.

Recommended Products/Accessories

- 5475-59 Frameless sliding shower door
- 5477-59 Frameless sliding shower door
- 5970-59 Framed sliding shower door
- 5975-59 Framed sliding shower door
- 5976-59 Framed sliding shower door
- 5977-59 Framed sliding shower door
- 547808-59 Frameless sliding shower door
- 572075-59 Framed sliding shower door
- 581075-59 Frameless sliding shower door
- K-23726 Drain treatment
- K-23723 Faucet cleaner
- K-23733 Vikrell® cleaner

Included Components

Product consists of:

- 72245103-V 36" end wall set with Aging in Place grab bars
- 72271100 60" x 36" shower base
- 72272103-V 60" shower back wall with Aging in Place grab bars



Codes/Standards

- CSA B45.5/IAPMO Z124
- ASTM E162
- ASTM E662
- HUD, UM Bulletin 73



Warranty – Bathing Fixtures (and Kitchen and Utility Sinks Made of Solid Vikrell® Material)

STERLING® Warranty - Grab Bars

See website for detailed warranty information.

Available Colors/Finishes

Color tiles intended for reference only.


Color	Code	Description
	0	White
	96	KOHLER Biscuit

1-800-STERLING (1-800-783-7546)

Kohler Co. reserves the right to make revisions without notice to product specifications.

For the most current Specification Sheet, go to www.sterlingplumbing.com.

8-22-2020 13:57 - US



Technical Information

All product dimensions are nominal.

- Installation: Three-wall alcove
 Drain location: Center
 Drain hole diameter: 3-5/16" (84 mm)
 Minimum flat for door: 3-1/4" (83 mm)
 Threshold height: 3-1/2" (89 mm)
 Maximum door height: 72" (1829 mm)
 Maximum door width: 56-5/8" (1438 mm)

Notes

- Install this product according to the installation instructions.
 Studs should be positioned roughly as shown.
 Double studding is recommended for pivot shower door installations.
 Attach grab bars at the specified backerboard locations only.
 Shower base cannot be installed without the wall surround.