
STERLING


STRONG. PROFESSIONAL. DESIGN.™


SPECIFICATIONS


# Bath Classics™ Vista Glide II™ Designer Pivot Shower Door

Models 1500D, 1502D, 1503D, 1505D, 1530D, 1562D, 1595D









## Standard Features

- Anodized aluminum-framed swinging glass doors
- Fits most fiberglass surround units
- Nylon pivot bushings provide silent operation
- Slanted threshold directs water back into shower
- Tempered glass ensures maximum safety
- Frame components extruded from aluminum alloy 6063-T5
- Adjustable wall jamb allows for out-of-plumb conditions up to 1" per side
- Installs left- or right-handed
- All necessary hardware included

## Standards and Ratings

- Tempered glass complies with ANSI Z97.1-1984 and Architectural Glazing Standard 16CFR1201

## Optional Features


- Bright silver, polished brass, or bright gold frame finishes
- Pebbled texture, cut crystal, symmetry (vertical striped), horizontal striped, cameo pattern, or clear glass panels
- Available to fit openings from 23"-48"
- Available in 66" height

| Features | Benefits |
|---|---|
| **Tempered glass** | Tempered glass offers maximum safety and durability. |
| **Full-length handle** | Full-length door handle allows for easy use by adults or children. |
| **Easy-to-clean threshold** | Bottom threshold directs water back into stall and minimizes soap or lint build up. |
| **Wide size adjustment** | Minimum size adjustment of 3-1/2” per model to reduce inventory requirements. |
| **Hide-away towel/robe hook** | Convenient hook swings in for wet items, swings out for robes and towels. |
| **Stainless steel hardware** | Prevents fasteners from rusting or corroding in a damp environment. |


# Bath Classics™
# Vista Glide II™
# Designer Pivot Shower Door


Models 1500D, 1502D, 1503D,
1505D, 1530D, 1562D, 1595D

D I M E N S I O N S



SECTION A-A




| Model | Frame Finish | Glass Panel Pattern | Min. Opening | Max. Opening | Height |
|---|---|---|---|---|---|
| 1500D-26S | Silver | Pebbled Texture | 23" | 26-1/2" | 66" |
| 1500D-27S | Silver | Pebbled Texture | 24" | 27-1/2" | 66" |
| 1500D-31S | Silver | Pebbled Texture | 27-1/2" | 31-1/4" | 66" |
| 1500D-36S | Silver | Pebbled Texture | 31-1/4" | 36" | 66" |
| 1500D-42S | Silver | Pebbled Texture | 36" | 42" | 66" |
| 1500D-42G | Polished Brass | Pebbled Texture | 36" | 42" | 66" |
| 1500D-48S | Silver | Pebbled Texture | 42" | 48" | 66" |
| 1500D-48G | Polished Brass | Pebbled Texture | 42" | 48" | 66" |
| 1502D-26S | Silver | Clear/Beige Stripes | 23" | 26-1/2" | 66" |
| 1502D-26G | Polished Brass | Clear/Beige Stripes | 23" | 26-1/2" | 66" |
| 1502D-27S | Silver | Clear/Beige Stripes | 24" | 27-1/2" | 66" |
| 1502D-27G | Polished Brass | Clear/Beige Stripes | 24" | 27-1/2" | 66" |
| 1502D-31S | Silver | Clear/Beige Stripes | 27-1/2" | 31-1/4" | 66" |
| 1502D-31G | Polished Brass | Clear/Beige Stripes | 27-1/2" | 31-1/4" | 66" |
| 1502D-36S | Silver | Clear/Beige Stripes | 31-1/4" | 36" | 66" |
| 1502D-36G | Polished Brass | Clear/Beige Stripes | 31-1/4" | 36" | 66" |
| 1502D-42S | Silver | Clear/Beige Stripes | 36" | 42" | 66" |
| 1502D-42G | Polished Brass | Clear/Beige Stripes | 36" | 42" | 66" |
| 1502D-48S | Silver | Clear/Beige Stripes | 42" | 48" | 66" |
| 1502D-48G | Polished Brass | Clear/Beige Stripes | 42" | 48" | 66" |
| 1503D-31S | Silver | Gray/Vertical Stripe | 27-1/2" | 31-1/4" | 66" |
| 1503D-36S | Silver | Gray/Vertical Stripe | 31-1/4" | 36" | 66" |
| 1503D-36PB | Polished Brass | Brown/Vertical Stripe | 31-1/4" | 36" | 66" |
| 1505D-42S | Silver | Clear | 36" | 42" | 66" |
| 1505D-42G | Polished Brass | Clear | 36" | 42" | 66" |
| 1505D-48S | Silver | Clear | 42" | 48" | 66" |
| 1505D-48G | Polished Brass | Clear | 42" | 48" | 66" |
| 1530D-36S | Silver | Clear/Cut Crystal | 31-1/4" | 36" | 66" |
| 1530D-36G | Polished Brass | Clear/Cut Crystal | 31-1/4" | 36" | 66" |
| 1562D-27S | Silver | Clear/White Stripes | 24" | 27-1/2" | 66" |
| 1562D-27PB | Polished Brass | Clear/White Stripes | 24" | 27-1/2" | 66" |
| 1562D-31S | Silver | Clear/White Stripes | 27-1/2" | 31-1/4" | 66" |
| 1562D-31PB | Polished Brass | Clear/White Stripes | 27-1/2" | 31-1/4" | 66" |
| 1562D-31W | White | Clear/White Stripes | 27-1/2" | 31-1/4" | 66" |
| 1562D-36S | Silver | Clear/White Stripes | 31-1/4" | 36" | 66" |
| 1562D-36PB | Polished Brass | Clear/White Stripes | 31-1/4" | 36" | 66" |
| 1562D-36W | White | Clear/White Stripes | 31-1/4" | 36" | 66" |
| 1595D-27S | Silver | Cameo | 24" | 27-1/2" | 66" |
| 1595D-27PB | Polished Brass | Cameo | 24" | 27-1/2" | 66" |
| 1595D-31S | Silver | Cameo | 27-1/2" | 31-1/4" | 66" |
| 1595D-31PB | Polished Brass | Cameo | 27-1/2" | 31-1/4" | 66" |
| 1595D-36S | Silver | Cameo | 31-1/4" | 36" | 66" |
| 1595D-36PB | Polished Brass | Cameo | 31-1/4" | 36" | 66" |

bema
BATH ENCLOSURE MANUFACTURERS ASSOCIATION

STERLING
STRONG. PROFESSIONAL. DESIGN.™

★ Made in U.S.A.

© 2001 Sterling Plumbing, 444 Highland Drive, Kohler, WI 53044 1-888-STERLING

Pub. No. 94136 01/02

www.sterlingplumbing.com

Printed in U.S.A.

Fixture dimensions are nominal and conform to tolerances established by ANSI Standards, Z124.1.