



**Mendota®**  
60" x 32" alcove bath, left drain  
**K-505**

### Features

- Safeguard® slip-resistant surface provides excellent traction underfoot
- 60"L x 32"W x 16-1/4"H
- Standard 5' x 32" size for alcove installation
- Integral apron for quick installation
- Integral lumbar support

### Material

- KOHLER® enameled cast iron

### Installation

- Alcove
- Integral flange
- Left drain

### Required Products/Accessories

K-T37391 Rotary-turn bath drain trim  
K-T37392 Rotary-turn bath drain trim

or

K-37383 Rough-in cable bath drain, PVC, 30" cable with tubing  
K-78438 30" cable bath drain

### Recommended Products/Accessories

K-1491 Bath/Whirlpool Pillow  
K-1601 Bath/whirlpool footstop, removable  
K-7213 27" Cable Bath Drain  
K-7214 27" Cable Bath Drain  
K-7259 Brass toe tap bath drain  
K-706000-D3 Frameless Sliding Bath Door  
K-706000-L 62" H sliding bath door with 1/4"-thick glass  
K-706004-D3 Frameless Sliding Bath Door  
K-706004-L Frameless Sliding Bath Door  
K-23726 Drain treatment  
K-23725 Cast iron cleaner  
K-31796 Above-the-floor bath drain kit  
K-31798 Bath drain kit



**ADA**

### Codes/Standards

ASME A112.19.1/CSA B45.2  
ASTM F462  
ADA  
ICC/ANSI A117.1  
IAPMO Certification

### KOHLER® Enameled Cast Iron Bath and Shower Base Lifetime Limited Warranty

See website for detailed warranty information.

### Available Colors/Finishes

*Color tiles intended for reference only.*

| Color | Code | Description |
|-------|------|-------------|
|-------|------|-------------|

|                                                                                     |    |         |
|-------------------------------------------------------------------------------------|----|---------|
|  | 0  | White   |
|  | 96 | Biscuit |


1-800-4KOHLER (1-800-456-4537)

Kohler Co. reserves the right to make revisions without notice to product specifications.


For the most current Specification Sheet, go to [www.kohler.com](http://www.kohler.com) USA or [www.kohler.ca](http://www.kohler.ca) Canada

6-8-2024 20:45 - US

THE BOLD LOOK  
OF **KOHLER®**



No change in measurements if connected with drain illustrated. (K-7160-TF)



## Technical Information

All product dimensions are nominal.

|                        |                                                   |
|------------------------|---------------------------------------------------|
| Drain location:        | Left                                              |
| Basin area, bottom:    | 46" x 20" (1168 mm x 508 mm)                      |
| Basin area, top:       | 54" x 24" (1372 mm x 610 mm)                      |
| Weight:                | 351 lbs (159.2 kg)                                |
| Minimum floor load:    | 56 lbs/ft <sup>2</sup> (273.4 kg/m <sup>2</sup> ) |
| Water depth:           | 10-7/8" (276 mm)                                  |
| Water capacity:        | 45 gal (170.3 L)                                  |
| Minimum flat for door: | 1-5/16" (33 mm)                                   |

## Notes

Measure your actual product for rough-in details.

Install this product according to the installation instructions.

The hot water supply should be 70% of the capacity of the bath or greater. Installations will vary.

Measure your actual product for roughing-in details.

Hot water supply should be 70% of capacity or greater. Installations will vary.

ADA compliant when installed to the specific requirements of these regulations.