

Mira Mode Maxim Dual Shower

Digital Mixer

An Immersive
showering experience
like no other.

Product Information

Description	Colour	Product No.
Mira Mode Maxim Dual Shower, Rear Fed (High Pressure)	Chrome	1.1907.001
Mira Mode Maxim Dual Shower, Rear Fed (Pumped for Gravity)	Chrome	1.1907.002
Mira Mode Maxim Dual Shower, Ceiling Fed (High Pressure)	Chrome	1.1907.003
Mira Mode Maxim Dual Shower, Ceiling Fed (Pumped for Gravity)	Chrome	1.1907.004

Features & Benefits

Temperature control

An Immersive showering experience from the luxurious 30cm deluge showerhead, featuring Mira's unique CloudCore™ technology, delivering a saturating mist spray.

Thermostatic temperature stability with digital intelligence

Indicator light signals when shower has reached desired temperature

Maximum temperature setting for increased safety

Easy to fit & maintain

Replaceable checkvalve and filters

Supplied with push fit isolators

For your customer

Flow rate: up to 16 l/min at 1 bar (High Pressure)
and at 0.1 bar (Pumped)

Rotary temperature control dial

Personalise showering settings using the Mira Mode app

30cm deluge head and Mira Switch showerhead



SUITABLE FOR ALL SYSTEMS



5 YEAR WARRANTY



MIRA MODE MAXIM DUAL
REAR FED



MIRA MODE MAXIM DUAL
CEILING FED

Product Specification

Tech Details

Installation Units & Fittings

Water Entry Points - Back, Rear Fed; Top, Ceiling Fed

Inlet Connections: 15mm push fit isolators (supplied) or 15mm compression

Data Connection to Digital Mixer: Low Voltage Data Cable

Digital Mixer

Inlet Connections: 15mm push fit isolators (supplied) or 15mm compression

Outlet connection: 15mm push fit isolators (supplied) or 15mm compression

Data Connection to control unit and fittings: Low Voltage Data Cable

Supply voltage: 230v +10%

Supply rating: 3 amp

Supply Conditions

Minimum maintained pressure:
Pumped: 0.01 bar (10 cm head); High Pressure: 1.0 bar (10 metre head)

Maximum maintained pressure:
Pumped: 1.0 bar (10 metre head); High Pressure: 5.0 bar (50 metre head)

Maximum static pressure:
Pumped: 1.0 bar (10 metre head); High Pressure: 10.0 bar (100 metre head)

Performance

Flow rate: up to 16 l/min at 0.1 bar (Pumped); 1 bar (High Pressure)

Temperature stability: $\pm 1^\circ\text{C}$

Safety Features

Phase shutdown Yes

Factory set to safe max temp: Factory set at 45°C

Approvals


WRAS approved

KIWA UK approved product




Dimensions


High Pressure Dual Outlet



Low Pressure Dual Outlet



User Interface



Remote Start/Stop

