Bardon™

Manual Flushometer and Urinal

K-72518



Features

- Washout
- 0.125 gpf (0.5 lpf)
- 3/4" top spud.
- Chloramine resistance on all rubber components exposed to waterway.
- 14-inch extended rim allows for ADA installation.

Technology

- Reliable piston valve technology.

Installation

- Wall-mount

Components

Product includes:

K-4904-ET High Efficiency Urinal (HEU)
K-13520 Manual 1/8 GPF Urinal Flushometer

ADA | **CSA B651**

Codes/Standards

ASME A112.18.1/CSA B125.1
ASME A112.19.2/CSA B45.1
CSA B64
CSA B125.3
ASSE 1037/ASME A112.1037/CSA B125.37
DOE - Energy Policy Act 1992
EPA WaterSense®
ADA
ICC/ANSI A117.1
CSA B651

KOHLER® One-Year Limited Warranty


See website for detailed warranty information.

Bardon™

Manual Flushometer and Urinal

K-72518

*Critical level must be maintained a minimum of 6" (152 mm) above the fixture inlet.



Technical Information

All product dimensions are nominal.

Flush outlet technology:	Washout
Spud size:	3/4", Inlet, Top
Spud size:	2", Outlet, Rear

Pressure and Supply Requirements

Fixture pressure min (static):	35 psi (241.3 kPa)
Fixture pressure max (static):	80 psi (551.6 kPa)

Notes

Install this product according to the installation guide.

ADA, CSA B651 compliant when installed to the specific requirements of these regulations.