



# KENDALE™ RECEPTOR

## Model ACR20476 DTA~B

### ACRYLIC



Model ACR20476DTA



Model ACR20476DTB

**Model ACR20476 DTA**  
(Low Threshold, Double Threshold)

**Model ACR20476 DTB**  
(Low Threshold, Double Threshold)

Length: 60" (1524mm)  
Width: 36" (914mm)  
Overall Height: 5 7/8" (149mm)  
Threshold Height: 4 3/8" (111 mm)

Shipping Weight: 60lbs. (27Kg)

Materials: Manufactured from a one-piece acrylic sheet, reinforced with fiberglass.

Hytec manufactures acrylic receptors to satisfy every bathroom design or decorating need. Raised tiling flanges allow for professional installation and finishing.

**Standard Features:**

- Easy to clean high gloss surface
- Chip and mar resistant
- Moulded-in floor pattern
- Raised tile ledge
- Wide threshold

**Colours:**

- Standard: White, Almond (Bone) or Biscuit
- Optional: Kohler Colours

**Options:**



- Single flange (SF)


All products manufactured by Hytec are covered by a comprehensive five-year limited warranty from the date of sale to the original owner. See the Hytec Bathing Fixtures List Price Book for further details.

**Hytec Plumbing Products**

(Division of Kohler Canada Co.)  
4150 Spallumcheen Dr, Armstrong BC V0E 1B6  
Ph. (800) 871-8311 (250) 546-3196 Fax (250) 546-3170

Double Flange - Standard     Single Flange (SF) - Option





Measurement tolerances  $\pm 1/4"$  (6.3mm)

All bathing fixtures comply with the applicable Canadian Standards.

EPA TSCA Title VI Compliant Product

For installation instructions please refer to our website HYTEC.CA

This sheet approximately describes products and equipment manufactured or supplied by Hytec Plumbing Products. Because of ongoing efforts to improve both design and quality, products and equipment actually furnished may differ without prior notice.

**Hytec Plumbing Products**

(Division of Kohler Canada Co.)  
4150 Spallumcheen Dr, Armstrong BC V0E 1B6  
Ph. (800) 871-8311 (250) 546-3196 Fax (250) 546-3170

