

Mira Apt ERD

Mixer Shower



SUITABLE FOR ALL SYSTEMS



5 YEAR WARRANTY

Clean chrome aesthetic meets reliable performance with dual outlet showering.



Product Information

Description	Colour	Product No.
Mira Apt ERD	Chrome	1.1878.008

Features & Benefits

Temperature control

Thermostatic temperature stability

Easy to fit

Fast-fix kit for easy installation

Front of tile installation system

Pipe spacer guide included to aid pipework installation during first fix

Front of tile installation system allows connection to pipework during second phase fix after tiling is complete

For your customer

Works on all systems, even at low pressure

Separate flow and temperature controls

Maximum temperature stop for increased safety (with override for a hotter shower)

Ceramic flow control ensures smooth reliable operation and allows water to be diverted to either the shower handset or shower overhead

Mira Cool Shield™ to ensure valve doesn't get hot during showering

Mira Magni-flo™ technology delivers up to 3x more flow, even at low pressure

One spray 9cm showerhead with rub-clean nozzles

Large 20cm deluge showerhead with rub-clean nozzles

1.25m flexible shower hose

Product Specification

Tech Details

Temperature and flow control

Temperature control type: Thermostatic

Flow control type: Ceramic

Installation

Water entry points: Rear only

Inlet connections: 15mm compression joints with pipes;
3/4" BSP connection to mixer shower

Outlet connections: 1/2" BSP Male

Reversed inlets supported: No = hot left, cold right only

Supply Conditions (hot and cold)

Cold water range: 1°C to 25°C

Hot water range: Min 55°C; 60°C - 65°C (recommended)

Minimum maintained pressure (gas water heater) :
1 bar (10 metre head)

Minimum maintained pressure (gravity system) : 0.1 bar (1 metre head)

Maximum maintained pressure: 5.0 bar (50 metre head)

Maximum static pressure: 10.0 bar (100 metre head)

Performance

Flow rate (at handset): 9 l/min at 0.5 bar

Temperature stability: ± 2°C

Safety Features

Automatic shutdown: Shutdown within 2 secs

Factory set to safe max temp

Adjustable maximum temperature for on-site conditions

Approvals

KIWA UK approved product

WRAS approved (Water Regulations Advisory Scheme)

TMV2 approved product



Dimensions

