

Mira Evoco Dual

Mixer Shower



SUITABLE FOR ALL SYSTEMS



5 YEAR WARRANTY

Beauty. Built-in. With illuminating Mira HydroGlo™ technology fully concealed shower in three stunning finishes.

Product Information

Description	Colour	Product No.
Mira Evoco Dual Outlet Shower with HydroGlo™ Technology	Chrome	1.1967.002
Mira Evoco Dual Outlet Shower with HydroGlo™ Technology	Matt Black	1.1967.003
Mira Evoco Dual Outlet Shower with HydroGlo™ Technology	Brushed Nickel	1.1967.004
Mira Evoco Dual Valve Only with HydroGlo™ Technology	Chrome	1.1967.078

Features & Benefits

Temperature control

Thermostatic temperature stability

Easy to fit

Integrated push fit connections already included

Spanner free installation

Mira's innovative installation system, providing a simple first fix solution

Protective cover to minimise damage between first and 2nd fix

Flushing system provided to test connections prior to tiling

Suitable for rear wall and noggin installations

For your customer

Works on all systems, even at low pressure

Separate flow and temperature controls using button actuation

Maximum temperature stop for increased safety (with override for a hotter shower)

Choose your outlet - intuitive push button technology allows you to select the handset, overhead or both

Mira Cool Shield™ to ensure valve doesn't get hot during showering

Mira Magni-flo™ technology delivers up to 3x more flow, even at low pressure

One spray 11cm multi-mode showerhead with rub-clean nozzles

Large 25cm deluge showerhead with rub-clean nozzles

1.25m flexible shower hose

The latest illuminating technology, no wiring or batteries required. Mira HydroGlo™ delivers extra experiences with no extra hassle.



Product Specification

Tech Details

Temperature and flow control

Temperature control type: Thermostatic

Flow actuation: Push button

Installation

Water entry points: Bottom only

Inlet connections: Direct 15mm push fit connections

Outlet connections: 15mm copper pipework

Reversed inlets supported: No = hot left, cold right only

Supply Conditions (hot and cold)

Cold water range: 1°C to 25°C

Hot water range: Min 55°C; 60°C - 65°C (recommended)

Minimum maintained pressure (gas water heater) : 1 bar (10 metre head)

Minimum maintained pressure (gravity system) : 0.1 bar (1 metre head)

Maximum maintained pressure: 5.0 bar (50 metre head)

Maximum static pressure: 10.0 bar (100 metre head)

Performance

Flow rate at 0.5 bar: 8.2 l/min (at Handset), 10.51 l/min (at Deluge)

Flow regulator: 9 l/min (supplied with product - x2)

Temperature stability: $\pm 2^\circ\text{C}$

Safety Features

Automatic shutdown: Shutdown within 2 secs

Factory set to safe maximum temperature

Adjustable maximum temperature for on-site conditions

Approvals

KIWA UK approved product

WRAS approved (Water Regulations Advisory Scheme)

TMV2 approved product

CE approved product

UKCA approved product



Dimensions

