

Mira Relate Matt Black EV

Mixer Shower Range



SUITABLE FOR ALL SYSTEMS



5 YEAR GUARANTEE

With Mira's ultra-durable new Matt Black finish, the Mira Relate Matt Black EV combines premium aesthetics with uncompromising quality.

Product Information

Description	Colour	Product No.
Mira Relate EV	Matt Black	1.1836.466

Features & Benefits

Temperature control

Thermostatic temperature stability

Easy to fit

Fast-fix kit for easy installation

Adjustable slide bar covers over previous fittings

Pipe spacer guide included to aid pipework installation during first fix

Front of tile installation system allows connection to pipework during second phase fix after tiling is complete

For your customer

Works on all systems, even at low pressure

Separate flow and temperature controls

Maximum temperature stop for increased safety (with override for a hotter shower)

Ceramic flow control ensures smooth reliable operation throughout the life of your product

Mira Cool Shield™ to ensure valve doesn't get hot during showering

Mira Magni-flo™ technology delivers up to 3x more flow, even at low pressure

Four spray 110 mm showerhead with rub-clean nozzles

1.25 m flexible smooth shower hose



Product Specification

Tech Details

Temperature and flow control

Temperature control type: Thermostatic

Flow control type: Ceramic

Installation

Water entry points: Rear only

Inlet connections: 15 mm compression joints with pipes;
¾" BSP connection to mixer shower

Outlet connections: ½" BSP Male

Reversed inlets supported: No = hot left, cold right only

Supply Conditions (hot and cold)

Cold water range: 1°C to 25°C

Hot water range: Min 55°C; 60°C - 65°C (recommended)

Minimum maintained pressure (gas water heater) :
1 bar (10 metre head)

Minimum maintained pressure (gravity system) : 0.1 bar (1 metre head)

Maximum maintained pressure: 5.0 bar (50 metre head)

Maximum static pressure: 10.0 bar (100 metre head)

Performance

Flow rate (at handset): 9 L/min at 0.5 bar

Temperature stability: ± 2°C

Safety Features

Automatic shutdown: Shutdown within 2 secs

Factory set to safe maximum temperature

Adjustable maximum temperature for on-site conditions

Approvals


KIWA UK approved product

WRAS approved (Water Regulations Advisory Scheme)

TMV2 approved product



Dimensions



mira
SHOWERS