



# Whiston®

## 36"x36" Pivot Door w/ Return

### 572084-36

#### Features

- Frameless, 1/4-inch-thick (6mm) clear tempered glass.
- Includes a 36-inch-wide glass return panel to create a corner enclosure.
- Magnetic seal keeps door firmly closed, providing excellent water containment.
- Knob handle keeps the design line simple and unobstructed.
- Low threshold (1-3/4-inch) for easy entry and exit.
- Adjustable ball catch for reliable operation.
- CleanCoat® glass treatment repels water for improved ease of cleaning.
- Available in Silver (S) finish.
- Door swings outward and can be installed to open right or left, depending on your preference.
- Pre-assembled frame and out-of-plumb adjustability for simple installation with no cutting.
- 1-inch width adjustability on each wall jamb, offering 2-inch total adjustability.

#### Installation

- Not for use in hospitality.
- For residential use only.

#### Optional Products/Accessories

1296811 Whiston™ Door Filler Jamb

#### Included Components

Product consists of:

572102-36 36" Pivot Door

572077-36 36" Return Panel

Additional Components:

Hardware kit



#### Codes/Standards

ANSI Z97.1

CPSC 16CFR 1201

#### STERLING® Warranty - Bath and Shower Doors

See website for detailed warranty information.

#### Available Colors/Finishes

*Color tiles intended for reference only.*

Color	Code	Description
-------	------	-------------

	S	
--	---	--

#### Available Glass Options

Code	Description
------	-------------

G05	Clear
-----	-------


---

1-800-STERLING (1-800-783-7546)

Kohler Co. reserves the right to make revisions without notice to product specifications.

For the most current Specification Sheet, go to [www.sterlingplumbing.com](http://www.sterlingplumbing.com).

4-25-2019 23:05 - US/CA



**Technical Information**

All product dimensions are nominal.

Installation type: For shower base installation

Opening Width - Min: 33-1/4" (845 mm)

Opening Width - Max: 35-1/4" (895 mm)

Walk-through - Min: 26" (660 mm)

Walk-through - Max: 26" (660 mm)

Glass thickness: 1/4" (6 mm)

Glass coating: CleanCoat®

**Notes**

Install this product according to the installation instructions.

The vertical opening should be a minimum of 75" (1905 mm) to allow for installation clearance.