



Whiston®

60"x36" Sliding Door w/ Return

572096-59

Features

- Frameless, 1/4-inch-thick (6mm) clear tempered glass.
- Includes a 36-inch-wide return panel to create a corner enclosure.
- Double rollers provide a smooth gliding action to give a quality feel for years to come.
- Magnetic seal keeps door firmly closed, providing excellent water containment.
- Knob handle keeps the design line simple and unobstructed.
- Low threshold (1-3/4-inch) for easy entry and exit.
- CleanCoat® glass treatment repels water for improved ease of cleaning.
- Detachable bottom rollers for ease of cleaning.
- Available in Silver (S) finish.
- Door can be installed to open right or left, depending on your preference.

Installation

- Not for use in hospitality.
- For residential use only.

Recommended Products/Accessories

1296811 Whiston™ Door Filler Jamb

Included Components

Product consists of:

572108-59 60" Sliding Door

572077-36 36" Return Panel

Additional Components:

Hardware kit



Codes/Standards

ANSI Z97.1

CPSC 16CFR 1201

STERLING® Warranty - Bath and Shower Doors

See website for detailed warranty information.

Available Colors/Finishes

Color tiles intended for reference only.


Color	Code	Description
-------	------	-------------

	S	
--	---	--

Available Glass Options

Code	Description
------	-------------

G05	Clear
-----	-------



* Walk-through

*25-1/2" (648 mm)

Technical Information

All product dimensions are nominal.

Installation type: For shower base installation

Opening Width - Min: 56-7/8" (1445 mm)

Opening Width - Max: 58-7/8" (1495 mm)

Walk-through - Min: 25-1/2" (648 mm)

Walk-through - Max: 25-1/2" (648 mm)

Glass thickness: 1/4" (6 mm)

Glass coating: CleanCoat®

Notes

Install this product according to the installation instructions.

The vertical opening should be a minimum of 75" (1905 mm) to allow for installation clearance.