



Whiston®

Frameless sliding shower door with return panel

572096-59

Features

- Frameless, 1/4" (6 mm) thick Clear tempered glass
- Includes a 36" (914 mm) wide glass return panel to create a corner enclosure
- Low, 1 3/4" (44 mm) threshold for easy entry and exit
- CleanCoat®+ glass coating creates a hydrophobic barrier that repels water, soap scum, and residue, saving time and protecting shower doors 10 times longer than original CleanCoat. (Based on 2021 internal wear/abrasion testing using a microfiber cloth.)

Technology

- Double rollers provide a smooth gliding action to give a quality feel for years to come
- Magnetic seal keeps door firmly closed, providing excellent water containment
- Knob handle keeps the design line simple and unobstructed
- Detachable bottom rollers for ease of cleaning

Installation

- Door can be installed to open to the left or right to suit your bathroom layout
- Not for use in hospitality
- For residential use only

Recommended Products/Accessories

1296811 Whiston™ Door Filler Jamb

Included Components

572077-36 36" return panel



Codes/Standards

ANSI Z97.1

CAN/CGSB-12.1

CPSC 16CFR 1201

STERLING® Bath and Shower Doors Five-Year Limited Warranty

See website for detailed warranty information.

Available Glass Options

Code	Description
------	-------------

G05	Clear
-----	-------


DISCONTINUED This product has been discontinued.

1-800-STERLING (1-800-783-7546)

Kohler Co. reserves the right to make revisions without notice to product specifications.

For the most current Specification Sheet, go to www.sterlingplumbing.com.

3-25-2024 21:12 - US



Technical Information

All product dimensions are nominal.

Base-To-Wall 1" (25 mm)

Radius – Max:

Notes

Install this product according to the installation instructions.

The vertical opening should be a minimum of 75" (1905 mm) to allow for installation clearance.