



Whiston®

Frameless sliding shower door with return panel

572096-59

Features

- Frameless, 1/4" (6mm) thick Clear tempered glass.
- CleanCoat® nanotechnology provides a smooth, nonstick surface to help prevent buildup of water stains, bacteria and mildew on your glass, to make it easy to clean and keep it looking like new.

Technology

- Includes a 36-inch-wide return panel to create a corner enclosure.
- Double rollers provide a smooth gliding action to give a quality feel for years to come.
- Magnetic seal keeps door firmly closed, providing excellent water containment.
- Knob handle keeps the design line simple and unobstructed.
- Low threshold (1-3/4-inch) for easy entry and exit.
- Detachable bottom rollers for ease of cleaning.

Installation

- Door can be installed to open to the left or right to suit your bathroom layout.
- Not for use in hospitality.
- For residential use only.

Recommended Products/Accessories

- 1296811 Whiston™ Door Filler Jamb
- K-23723 Faucet cleaner

Included Components

Product consists of:

- 572108-59 Frameless sliding shower door
- 572077-36 36" return panel

Additional Components:

- Hardware kit



Codes/Standards

- ANSI Z97.1
- CPSC 16CFR 1201

STERLING® Warranty - Bath and Shower Doors

See website for detailed warranty information.

Available Colors/Finishes

Color tiles intended for reference only.


Color Code Description

	S	Silver
--	----------	--------

Available Glass Options

Code Description

G05	Clear
-----	-------



Technical Information

All product dimensions are nominal.

Installation type: For shower base installation

Opening Width - Min: 56-7/8" (1445 mm)

Opening Width - Max: 58-7/8" (1495 mm)

Walk-through - Min: 25-1/2" (648 mm)

Walk-through - Max: 25-1/2" (648 mm)

Base-To-Wall Radius 1" (25 mm)

- Max:

Glass thickness: 1/4" (6 mm)

Glass coating: CleanCoat®

Notes

Install this product according to the installation instructions.

The vertical opening should be a minimum of 75" (1905 mm) to allow for installation clearance.